

**Garant**
**Socket set 3/8 inch, Number of tools: 15**

**Order data**

Order number	955165 15
GTIN	4062406158125
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 955165: 1 pc.

GARANT reversible ratchet, 3/8 inch No. 635025 size 3/8: 1 pc.

GARANT extension 3/8 inch No. 635429 size 125; 240: 1 pc. each

GARANT universal joint 3/8 inch No. 636229 size 3/8: 1 pc.

GARANT hexagon socket 3/8 inch "Surface Drive" No. 637125 size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 22: 1 pc. each

suitable for shadowboard depth: 115 mm

Width: 383 mm

Depth: 115 mm

**Technical description**

Number of tools	15
Width	383 mm
Depth	115 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Square drive	3/8 in

suitable for shadowboard depth	115 mm
Type of product	Rigid foam inlay

## Accessories

Extension, 3/8 inch overall length 240 mm	635429 240
Hexagon socket, 3/8 inch Surface Drive Width across flats 18 mm	637125 18
Reversible ratchet, 3/8 inch with ejector Type 3/8	635025 3/8
Hexagon socket, 3/8 inch Surface Drive Width across flats 10 mm	637125 10
Hexagon socket, 3/8 inch Surface Drive Width across flats 12 mm	637125 12
Hexagon socket, 3/8 inch Surface Drive Width across flats 15 mm	637125 15
Hexagon socket, 3/8 inch Surface Drive Width across flats 13 mm	637125 13
Universal joint 3/8 inch Type 3/8	636229 3/8
Hexagon socket, 3/8 inch Surface Drive Width across flats 19 mm	637125 19
Extension, 3/8 inch overall length 125 mm	635429 125
Rigid foam inlay for tool sets suitable for rigid foam set 955165	952001 955165
Hexagon socket, 3/8 inch Surface Drive Width across flats 22 mm	637125 22
Hexagon socket, 3/8 inch Surface Drive Width across flats 17 mm	637125 17
Hexagon socket, 3/8 inch Surface Drive Width across flats 14 mm	637125 14
Hexagon socket, 3/8 inch Surface Drive Width across flats 11 mm	637125 11
Hexagon socket, 3/8 inch Surface Drive Width across flats 16 mm	637125 16

