



Workshop set, Number of tools: 36



Order data

Order number	955017 36
GTIN	4062406158675
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Suitable for :

GARANT roller cabinets with full extension drawers and a drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Roller cabinets No. 914520 – 914582.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955017: 1 pc.

HOLEX combination spanner No. 613950 size 5.5; 7; 8; 10; 13; 16; 17; 18; 19: 1 pc. each

HOLEX reversible ratchet, 1/2 inch No. 640190 size 1/2: 1 pc.

HOLEX extension 1/2 inch No. 641020 size 130; 255: 1 pc. each

HOLEX T-handle 1/2 inch No. 641320 size 295: 1 pc.

HOLEX universal joint 1/2 inch No. 641620 size 1/2: 1 pc.

HOLEX bi-hex socket 1/2 inch No. 642120 size 13; 14; 15; 16; 17; 18; 19; 21; 22; 24: 1 pc. each

HOLEX bi-hex socket long 1/8 inch No. 642520 size 17; 19; 21: 1 pc. each

HOLEX slot-head screwdriver with power grip No. 660701, size 3.5; 5.5: 1 pc. each

HOLEX short slot-head screwdriver No. 664201 size 5.5: 1 pc.

HOLEX screwdriver for Phillips No. 668401 size 1; 2: 1 pc. each

HOLEX stub screwdriver for Phillips No. 668471 size 2: 1 pc.

HOLEX combination pliers, vanadium No. 703000 size 180: 1 pc.

HOLEX water pump pliers No. 706151 size 250: 1 pc.

HOLEX engineer's hammer No. 750125 size 300: 1 pc.
suitable for workstations and storage equipment: Roller cabinet

Width: 500 mm

Depth: 400 mm

Width in G: 20

Depth in G: 16

Technical description

Width in G	20
Depth in G	16
Width	500 mm
Depth	400 mm
Version	for roller cabinet drawer
suitable for drawer front height	75 mm
suitable for drawer front height	125 mm
suitable for drawer front height	200 mm
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	20×16
Square drive	1/2 in
suitable for workstations and storage equipment	Roller cabinet
Type of product	Rigid foam inlay

Accessories

Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642120 14
Combination spanner Width across flats 19 mm	613950 19
Screwdriver for Phillips, short Cross-head size 2	668471 2
Extension, 1/2 inch overall length 255 mm	641020 255
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642120 19
Water pump pliers with plastic coating overall length 250 mm	706150 250

Rigid foam inlay for tool sets suitable for rigid foam set 955017	952001 955017
Universal joint, 1/2 inch Type 1/2	641620 1/2
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642120 16
T-handle, 1/2 inch overall length 295 mm	641320 295
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642120 24
Combination spanner Width across flats 16 mm	613950 16
Bi-hexagon socket long, 1/2 inch Width across flats 17 mm	642520 17
Vanadium combination pliers, bright finished overall length 180 mm	703000 180
Combination spanner Width across flats 10 mm	613950 10
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2
Screwdriver for slot-head, short Blade width b 5,5 mm	664201 5,5
Combination spanner Width across flats 13 mm	613950 13
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642120 21
Water pump pliers with plastic coating Overall length 250 mm	706151 250
Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Combination spanner Width across flats 5,5 mm	613950 5,5
Combination spanner Width across flats 8 mm	613950 8
Screwdriver for slot-head, with power grip Blade width b 5,5 mm	660701 5,5
Screwdriver for slot-head, with power grip Blade width b 3,5 mm	660701 3,5
Engineer's hammer Weight without handle 300 g	750125 300
Combination spanner Width across flats 17 mm	613950 17
Extension, 1/2 inch overall length 130 mm	641020 130
Bi-hexagon socket long, 1/2 inch Width across flats 19 mm	642520 19
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642120 13
Bi-hexagon socket long, 1/2 inch Width across flats 21 mm	642520 21

Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642120 17
Combination spanner Width across flats 18 mm	613950 18
Combination spanner Width across flats 7 mm	613950 7
Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642120 15
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642120 22
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642120 18
Reversible ratchet, 1/2 inch with ejector	640220