

Garant**CNC tool trolley with solid rubber wheels, Usable width: 452mm****Order data**

Order number	970046 452
GTIN	4062406163112
Item class	91L

Description**Version:**

Sheet metal chassis and structure with side panels perforated on a 25 mm grid for attachment of carrier rails and tool carriers. Two ball bearing fixed wheels, two castors (with parking brake) (Ø 160 mm) and 4 large push handles ensure safe handling in all directions within the workshop area. With sheet metal shelf (L×W×D 150×452×30 mm).

Supplied with:

Tool trolley with 2 side panels, with push handle and solid rubber wheels.

Colour:

Chassis and side walls RAL 7016 anthracite grey **powder-coated**.

Note:

Suitable carrier rails for GARANT Tool UNIT toolholders can be found under No. 970110, GARANT Tool UNIT under No. 971000. Suitable tool carriers can be found under No. 970125 or No. 970130.

Technical description

Number of carrier rails (per side)	2
Footprint width	500 mm

Height	1200 mm
Usable width	452 mm
Footprint depth	800 mm
Depth	800 mm
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Number of tool carriers (per side)	4
maximum load capacity	400 kg
Wheel Ø	160 mm
Material of wheel	Solid rubber
Width	500 mm
Material thickness	0.9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC tool trolley

Accessories

Tool carrier with tool sockets for tool shanks HSK100	970125 HSK100
Tool carrier with tool sockets for tool shanks VDI30	970125 VDI30
Carrier rail for Tool UNIT tool carrier Width 452 mm	970110 452
Tool carrier with tool sockets for tool shanks HSK50	970125 HSK50
Tool carrier with tool sockets for tool shanks C5	970125 C5
Tool carrier with tool sockets for tool shanks HSK63	970125 HSK63
Tool carrier with tool sockets for tool shanks C8	970125 C8
Tool carrier with tool sockets for tool shanks SK40	970125 SK40
Tool carrier with tool sockets for tool shanks SK30	970125 SK30
Tool carrier with tool sockets for tool shanks SK50	970125 SK50
Tool carrier with tool sockets for tool shanks HSK40	970125 HSK40

Tool carrier with tool sockets for tool shanks HSK80	970125 HSK80
Tool carrier with tool sockets for tool shanks VDI20	970125 VDI20
Tool carrier with tool sockets for tool shanks 0	970125 0
Tool carrier with tool sockets for tool shanks VDI40	970125 VDI40
Tool carrier with tool sockets for tool shanks C6	970125 C6
Tool carrier with tool sockets for tool shanks C4	970125 C4