

Garant**CNC tool trolley with solid rubber wheels, Usable width: 627mm****Order data**

Order number	970046 627
GTIN	4062406163129
Item class	91L

Description**Version:**

Sheet metal chassis and structure with side panels perforated on a 25 mm grid for attachment of carrier rails and tool carriers. Two ball bearing fixed wheels, two castors (with parking brake) (Ø 160 mm) and 4 large push handles ensure safe handling in all directions within the workshop area. With sheet metal shelf (LxWxD 150x452x30 mm).

Supplied with:

Tool trolley with 2 side panels, with push handle and solid rubber wheels.

Colour:

Chassis and side walls RAL 7016 anthracite grey **powder-coated**.

Note:

Suitable carrier rails for GARANT Tool UNIT toolholders can be found under No. 970110, GARANT Tool UNIT under No. 971000. Suitable tool carriers can be found under No. 970125 or No. 970130.

Technical description

Height	1200 mm
Usable width	627 mm

maximum load capacity	400 kg
Number of castors with parking brake	2
Depth	800 mm
Number of carrier rails (per side)	2
Footprint width	675 mm
Width	675 mm
Number of fixed wheels without parking brake	2
Footprint depth	800 mm
Material of wheel	Solid rubber
Wheel Ø	160 mm
Number of tool carriers (per side)	4
Material thickness	0.9 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC tool trolley

Accessories

Tool carrier with tool sockets for tool shanks HSK63	970130 HSK63
Tool carrier with tool sockets for tool shanks C6	970130 C6
Tool carrier with tool sockets for tool shanks SK40	970130 SK40
Tool carrier with tool sockets for tool shanks C8	970130 C8
Tool carrier with tool sockets for tool shanks VDI20	970130 VDI20
Tool carrier with tool sockets for tool shanks HSK100	970130 HSK100
Carrier rail for Tool UNIT tool carrier Width 627 mm	970110 627
Tool carrier with tool sockets for tool shanks 0	970130 0
Tool carrier with tool sockets for tool shanks VDI30	970130 VDI30
Tool carrier with tool sockets for tool shanks SK30	970130 SK30
Tool carrier with tool sockets for tool shanks C4	970130 C4

Tool carrier with tool sockets for tool shanks VDI40	970130 VDI40
Tool carrier with tool sockets for tool shanks HSK80	970130 HSK80
Tool carrier with tool sockets for tool shanks HSK40	970130 HSK40
Tool carrier with tool sockets for tool shanks HSK50	970130 HSK50
Tool carrier with tool sockets for tool shanks SK50	970130 SK50
Tool carrier with tool sockets for tool shanks C5	970130 C5