

**ONE-KEY™ cordless hammer drill / driver, Type: M18OPD2-5****Order data**

Order number	070102 M18OPD2-5
GTIN	4058546224721
Item class	03L

Description**Version:**

- **Powerful cordless 2-speed hammer drill /screwdriver with multi-stage torque setting.**
- **REDLITHIUM-ION™ Red Li-ion batteries with single-cell monitoring and charge display.**
- **Sturdy metal gearbox for long working life.**
- **FIXTEC metal quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**
- **Brushless POWERSTATE™-motor (not size M18BPD4) for very high efficiency. Very low wear and up to 10 times the working life of standard DC motors.**
- **REDLINK PLUS™ electronics overload protection and power management.**

FUEL™ ONE-KEY™ – latest generation of the FUEL™ devices with **integral Bluetooth® technology for individual configuration, online stock management and device reporting.**

FUEL™ top model with high torque.

Advantage:

Brushless POWERSTATE™ motor.

Supplied with:

Supplied with 2 pcs. Li-ion batteries, charger, transport case (HD box) and belt clip.

Note:

See No. 073814 – 073816, 073827 and 073840 for suitable batteries and chargers.

The suitable Bluetooth tracking module can be found under 070103 BTT-1.

Technical description

Battery capacity	5 Ah
maximum twist drill size Ø in steel	16 mm
Weight	2.2 kg
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 1st speed	0 - 550 min ⁻¹
maximum twist drill size Ø in concrete	16 mm
maximum torque	135 Nm
maximum vibration to EN without hammer drill function	1.33 m/s ²
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN with hammer drill function	13.2 m/s ²
Battery voltage	18 V
App link	OneKey
typical application	Heavy Duty
Motor design	FUEL™
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum speed 2nd speed	2000 min ⁻¹
Manufacturer's designation	M18ONEPD2-502X
maximum twist drill size Ø in wood	89 mm
Power supply	Rechargeable battery-powered
Suitable for material	Stone
Suitable for material	Concrete
Suitable for material	Masonry
Type of product	limpact drill /screwdriver

Accessories

Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC