

Garant**Transport trolley with PU wheels, Usable width mm / model: 452/A****Order data**

Order number	970011 452/A
GTIN	4062406163136
Item class	91L

Description**Version:**

Sturdy chassis with 2 ball-bearing fixed wheels and 2 castors (with parking brake) (Ø 160 mm). The stiles are positively fitted to the chassis and the push handle, and bolted to them. Side panels are perforated with a 25 mm grid to accept carrier rails and tool carriers.

Supplied with:

Tool trolley with 2 side panels, with push handle and PU wheels.

Colour:

Body RAL 7035 light grey, side walls RAL 7016 anthracite grey **powder-coated**.

Note:

Suitable carrier rails for GARANT Tool UNIT toolholders can be found under No. 970110, GARANT Tool UNIT under No. 971000. Suitable tool carriers can be found under No. 970125 or No. 970130.

Technical description

Height	925 mm
Number of tool carriers (1 level)	5
Wheel Ø	160 mm

Number of fixed wheels without parking brake	2
Footprint width	500 mm
maximum load capacity	400 kg
Footprint depth	800 mm
Number of castors with parking brake	2
Material of wheel	PU
Usable width	452 mm
Model	A
Depth	800 mm
Number of carrier rails (1 level)	3
Width	500 mm
Material thickness	1.2 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC tool trolley

Accessories

Tool carrier with tool sockets for tool shanks HSK100	970125 HSK100
Tool carrier with tool sockets for tool shanks HSK50	970125 HSK50
Tool carrier with tool sockets for tool shanks SK40	970125 SK40
Tray with cover for modular tool trolley Width 452 mm	970175 452
Tool carrier with tool sockets for tool shanks VDI20	970125 VDI20
Tray for modular tool trolley Width 452 mm	970170 452
Tool carrier with tool sockets for tool shanks C4	970125 C4
Tool carrier with tool sockets for tool shanks VDI30	970125 VDI30
Tool carrier with tool sockets for tool shanks 0	970125 0
Tool carrier with tool sockets for tool shanks C6	970125 C6
Tool carrier with tool sockets for tool shanks HSK80	970125 HSK80

Tool carrier with tool sockets for tool shanks HSK40	970125 HSK40
Carrier rail for Tool UNIT tool carrier Width 452 mm	970110 452
Tool carrier with tool sockets for tool shanks VDI40	970125 VDI40
Tool carrier with tool sockets for tool shanks C5	970125 C5
Tool carrier with tool sockets for tool shanks C8	970125 C8
Tool carrier with tool sockets for tool shanks SK50	970125 SK50
Tool carrier with tool sockets for tool shanks SK30	970125 SK30
Tool carrier with tool sockets for tool shanks HSK63	970125 HSK63