

**PRYOR****Numeral punch set, 10 pieces Normal script 0 – 9, Character height: 6mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 085405 6      |
| GTIN         | 5022044000315 |
| Item class   | 08W           |

**Description****Version:**

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Normal script**; i. e. the punched character can be read directly on the component.

**Application:**

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

**Spare part:**

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

**Note:**

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

**Technical description**

|                 |     |
|-----------------|-----|
| Shank thickness | 9.5 |
|-----------------|-----|

|                  |            |
|------------------|------------|
| Depth limitation | yes        |
| overall length   | 70 mm      |
| Character height | 6 mm       |
| Type of product  | Hand punch |

## Accessories

|   |             |
|---|-------------|
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/1 | 085411 6/1  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/7 | 085411 6/7  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/2 | 085411 6/2  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/5 | 085411 6/5  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/3 | 085411 6/3  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/0 | 085411 6/0  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/8 | 085411 6/8  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/6 | 085411 6/6  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/9 | 085411 6/9  |
| Number punch – individual Normal script 0 – 9 Font height (mm) / characters 6/4 | 085411 6/4  |
| Punch holder Type GRIP  | 085475 GRIP |