

Garant GRIDLINE

**ESD casing 16G with drawers wheeled, 12×20G, Casing height mm / number of drawers: 500/4mm****Order data**

Order number	972022 500/4
GTIN	4062406166939
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock. With two ball-bearing fixed wheels and two castors (castors with brakes for the wheels and the castor heads) Ø 125 mm with abrasion-resistant, **conductive wheels**. Drawers with **individual drawer release system** prevents the opening of drawers during transport.

**Application:**

Drawer casing for individual fitting to the ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 or for ESD workbenches No. 972150 – 972195.

**Fitted with:**

Drawer front height, mm: 50; 75; 100; 200

**Colour:**

Body and drawers light grey similar to RAL7035, **ESD powder-coated**.

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive.

**Technical description**

Height	700 mm
Drawer usable depth	500 mm
Electronic locking system can be retrofitted	yes
Treadless tyres	yes
ComfortClose	no
with anti-roll lip	yes
Number of castors without parking brake	2
Individual drawer release system	One-hand
Drawer usable width	300 mm
Drawer usable width in G	12
Number of castors with parking brake	2
Number of drawers	4
Weight	54 kg
maximum load capacity	250 kg
Usable height	425 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable depth in G	20
Drawer body usable height	425 mm
Drawer usable area in G	12×20
Depth	650 mm
Width	400 mm
Version	wheeled
Version	with drawers
Usable height for drawers	425 mm
Material thickness	1 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	12×20G
Type of product	Assembly trolley

---

## Accessories

ESD drawer with one-handed individual drawer release system Drawer front height 100 mm	972036 100
ESD drawer with one-handed individual drawer release system Drawer front height 50 mm	972036 50
ESD drawer with one-handed individual drawer release system Drawer front height 75 mm	972036 75
ESD drawer with one-handed individual drawer release system Drawer front height 200 mm	972036 200
ESD casing 16G for individual configuration with drawerswheeled Height of the housing 500 mm	972032 500
Lock plate for GridLine Type KO21	914227 KO21