



## Cordless combi drill, Type: 7113236H1



### Order data

Order number	070100 7113236H1
GTIN	2050002046443
Item class	03F

### Description

#### Version:

**2-Speed cordless combi drill with brushless motor.**

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**
- **With QuickIN all-metal drill chuck (120 Nm) with carbide-coated jaws and high clamping forces.**
- **FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.**

#### Supplied with:

Supplied with 2 × 18 V / 6 Ah Li-ion battery, 1 × ALG 80 quick charger, 1 × QuickIN drill chuck (120 Nm), 1 × belt clip, 1 × bit garage, carrying case.

#### Note:

See No. 073851 – 073866 for suitable batteries and chargers.

### Technical description

Battery voltage	18 V
-----------------	------

Battery capacity	6 Ah
typical application	Heavy Duty
maximum twist drill size Ø in steel	13 mm
maximum torque soft	32 Nm
Motor design	Brushless
maximum torque hard	60 Nm
maximum vibration to EN with hammer drill function	13 m/s <sup>2</sup>
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Packaging	Carrying case
Quick-clamping chuck range	1.5 - 13 mm
maximum vibration to EN without hammer drill function	< 2.5 m/s <sup>2</sup>
maximum speed 1st speed	0 - 450 min <sup>-1</sup>
Manufacturer's designation	ASB 18 QC
Weight	1.8 kg
maximum twist drill size Ø in wood	50 mm
maximum speed 2nd speed	2000 min <sup>-1</sup>
maximum twist drill size Ø in concrete	13 mm
Power supply	Rechargeable battery-powered
Type of product	limpact drill /screwdriver

## Accessories

Accessories for drill / driversQuick-In Type HOLES AW	070208 HOLES AW
Accessories for drill / driversQuick-In Type CHUCK120	070208 CHUCK120
Accessories for drill / driversQuick-In Type CHUCK-SKE	070208 CHUCK-SKE
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion batteryHighPower Battery type, battery voltage FE18 V	073834 FE18

Accessories for drill / driversQuick-In Type THREAD-SET	070208 THREAD-SET
Offset screwdriving attachment Type WB1	073920 WB1
Accessories for drill / driversQuick-In Type 711301	070208 711301
Accessories for drill / driversQuick-In Type INCH14	070208 INCH14
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Accessories for drill / driversQuick-In Type INCH12	070208 INCH12
Accessories for drill / driversQuick-In Type ANGLE	070208 ANGLE
Offset screwdriving attachment Type OSD2	073920 OSD2
Accessories for drill / driversQuick-In Type CHUCK60	070208 CHUCK60
Battery starter set Type 92604323	073832 92604323
Cordless combi drill Type 71132364	070100 71132364