




## Socket set, 1/4; 3/8 inch square drive 48 pieces



### Order data

Order number	630006
GTIN	4018754260539
Item class	63A

### Description

#### Version:

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

#### Application:

For external hexagon screws / nuts with thread M2 – M14.

For spark plugs 16 mm.

For slot-head screws with thread M1.6 – M5.

For Phillips screws with thread M2 – M6.

For hexagon socket head screws with thread M4 – M10.

#### Material:

Chrome alloy steel, chrome-plated.

#### Supplied with:

1/4 inch hexagon socket set: 8 pcs. No. 631000 size 4; 4.5; 5; 5.5; 6; 7; 8; 9

3/8 inch hexagon socket set: 12 pcs. No. 637200 size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22

3/8 inch spark plug socket: 1 pc. No. 637310 size 16

BITS for Phillips C 6.3: 3 pcs. No. 675310 size 1/25; 2/25; 3/25

Bits for Pozidriv, C 6.3: 1 pc. No. 675320 size 2/25

Bits for slot-head, C 6.3: 6 pcs. No. 675250 size 3; 3.5; 4; 5.5; 6.5; 8

Bits for hex socket, C 6.3: 5 pcs. No. 675240 size 3; 4; 5; 6; 8

Bit adapter: 2 pcs. similar to No. 676800 size 4/4; 8/4

3/8 inch adaptor: 1 pc. No. 649505 size 3

3/8 inch tommy-bar: 1 pc. No. 635700 size 165

1/4 inch spinner handle: 1 pc. No. 632800 size 150

1/4 inch extension: 1 pc. No. 632400 size 150

3/8 inch extensions: 2 pcs. No. 63 5400 size 75; 240 mm  
 1/4 inch universal joint: 1 pc. No. 633500 size 1/4  
 3/8 inch universal joint: 1 pc. No. 636200 size 3/8  
 1/4 inch ratchet: 1 pc. No. 632000 size 1/4  
 3/8 inch ratchet: 1 pc. No. 635000 size 3/8  
 Presented in: ABS plastic box  
 Square drive: 1/4 inch  
 Square drive: 3/8 inch  
 Width across flats range, hexagon sockets: 4-22 mm  
 Width across flats range, hexagon wrenches: 3-8 mm

## Technical description

Drive profile	Hexagon socket
Drive profile	Hexagon screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for Phillips
Width across flats range, hexagon sockets	4-22 mm
Width across flats range, hexagon wrenches	3-8 mm
Number of pieces	48
Square drive	1/4 inch
Square drive	3/8 inch
Packaging	ABS plastic box
Length	413 mm
Width	230 mm
Height	57 mm
with QuickRelease	no
Type of product	Socket spanner

## Accessories

Hexagon socket, 1/4 inch Width across flats 4 mm	631000 4
--------------------------------------------------	----------

Hexagon socket, 1/4 inch Width across flats 4,5 mm	631000 4,5
Extension, 3/8 inch overall length 240 mm	635400 240
Spinner handle, 1/4 inch overall length mm	632800
Bit for Phillips, 1/4 inch Cross-head size / overall length 2/25 mm	675310 2/25
Hexagon socket, 3/8 inch Width across flats 13 mm	637200 13
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 6 mm	675240 6
Hexagon socket, 1/4 inch Width across flats 9 mm	631000 9
Hexagon socket, 3/8 inch Width across flats 19 mm	637200 19
Bit for Pozidriv, 1/4 inch Cross-head size / overall length 2/25 mm	675320 2/25
Hexagon socket, 3/8 inch Width across flats 15 mm	637200 15
Hexagon socket, 3/8 inch Width across flats 17 mm	637200 17
Bit for slot-head, 1/4 inch, 25 mm long Blade width 8 mm	675250 8
Universal joint, 3/8 inch Type 3/8	636200 3/8
Reversible ratchet, 1/4 inch Type	632000
Bit for slot-head, 1/4 inch, 25 mm long Blade width 4 mm	675250 4
Universal joint, 1/4 inch Type 1/4	633500 1/4
Bit for slot-head, 1/4 inch, 25 mm long Blade width 6,5 mm	675250 6,5
Hexagon socket, 1/4 inch Width across flats 8 mm	631000 8
Hexagon socket, 3/8 inch Width across flats 22 mm	637200 22
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 4 mm	675240 4
Bit for Phillips, 1/4 inch Cross-head size / overall length 1/25 mm	675310 1/25
Hexagon socket, 1/4 inch Width across flats 6 mm	631000 6
Hexagon socket, 1/4 inch Width across flats 5 mm	631000 5
Bit for slot-head, 1/4 inch, 25 mm long Blade width 3 mm	675250 3
Reducer piece Type 3	649505 3
Bit for slot-head, 1/4 inch, 25 mm long Blade width 5,5 mm	675250 5,5
Single hexagon socket for spark plugs 3/8 inch Width across flats 16 mm	637310 16

Bit for Phillips, 1/4 inch Cross-head size / overall length 3/25 mm	675310 3/25
Hexagon socket, 3/8 inch Width across flats 14 mm	637200 14
Hexagon socket, 3/8 inch Width across flats 11 mm	637200 11
Reversible ratchet, 3/8 inch Type	635000
Hexagon socket, 3/8 inch Width across flats 18 mm	637200 18
Extension, 1/4 inch overall length 150 mm	632400 150
Hexagon socket, 3/8 inch Width across flats 21 mm	637200 21
Hexagon socket, 3/8 inch Width across flats 16 mm	637200 16
Hexagon socket, 3/8 inch Width across flats 10 mm	637200 10
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 3 mm	675240 3
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631000 5,5
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 5 mm	675240 5
Hexagon socket, 3/8 inch Width across flats 12 mm	637200 12
Bit for hexagon, 1/4 inch Hex-plus profile Hexagon 8 mm	675240 8
Extension, 3/8 inch overall length 75 mm	635400 75
T-handle, 3/8 inch overall length 165 mm	635700 165
Hexagon socket, 1/4 inch Width across flats 7 mm	631000 7