



Socket set 3/8 inch square drive 33 pieces metric / imperial



Order data

Order number	634711
GTIN	4018754260430
Item class	63A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For hexagon head screws / nuts with thread M4 – M14, for nuts / bolts with thread up to 9/16 inch (American inch sizes).

Material:

Chrome alloy steel, chrome-plated.

Supplied with:

Bi-hexagon sockets: 16 pcs. No. 637000

size 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22

Bi-hexagon sockets: 12 pcs. No. 637100 size 1/4; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4; 13/16; 7/8

T-handle: 1 pc. No. 635700

Extensions: 2 pcs. No. 63 5400 size 75; 240 mm

Universal joint: 1 pc. No. 636200

Ratchet: 1 pc. No. 635000

Presented in: ABS plastic box

Technical description

Width across flats range, bi-hex sockets	7-22 mm
Width across flats range, bi-hex sockets	1/4-7/8 in

Width across flats	metric / imperial
Square drive	3/8 in
Number of pieces	33
Drive profile	Bi-hex socket
Length	413 mm
Width	230 mm
Height	57 mm
Type of product	Socket spanner

Accessories

Bi-hexagon socket, 3/8 inch Width across flats 18 mm	637000 18
Bi-hexagon socket, 3/8 inch Width across flats 3/8 in	637100 3/8
Bi-hexagon socket, 3/8 inch Width across flats 7/16 in	637100 7/16
Bi-hexagon socket, 3/8 inch Width across flats 13 mm	637000 13
Bi-hexagon socket, 3/8 inch Width across flats 11/32 in	637100 11/32
Bi-hexagon socket, 3/8 inch Width across flats 9/16 in	637100 9/16
Bi-hexagon socket, 3/8 inch Width across flats 5/16 in	637100 5/16
Bi-hexagon socket, 3/8 inch Width across flats 9 mm	637000 9
Extension, 3/8 inch overall length 240 mm	635400 240
Bi-hexagon socket, 3/8 inch Width across flats 15 mm	637000 15
Universal joint, 3/8 inch Type 3/8	636200 3/8
T-handle, 3/8 inch overall length 165 mm	635700 165
Bi-hexagon socket, 3/8 inch Width across flats 20 mm	637000 20
Bi-hexagon socket, 3/8 inch Width across flats 7 mm	637000 7
Extension, 3/8 inch overall length 75 mm	635400 75
Bi-hexagon socket, 3/8 inch Width across flats 11 mm	637000 11
Bi-hexagon socket, 3/8 inch Width across flats 17 mm	637000 17
Bi-hexagon socket, 3/8 inch Width across flats 3/4 in	637100 3/4

Bi-hexagon socket, 3/8 inch Width across flats 5/8 in	637100 5/8
Bi-hexagon socket, 3/8 inch Width across flats 19 mm	637000 19
Bi-hexagon socket, 3/8 inch Width across flats 16 mm	637000 16
Bi-hexagon socket, 3/8 inch Width across flats 12 mm	637000 12
Bi-hexagon socket, 3/8 inch Width across flats 14 mm	637000 14
Bi-hexagon socket, 3/8 inch Width across flats 1/2 in	637100 1/2
Bi-hexagon socket, 3/8 inch Width across flats 10 mm	637000 10
Bi-hexagon socket, 3/8 inch Width across flats 21 mm	637000 21
Bi-hexagon socket, 3/8 inch Width across flats 22 mm	637000 22
Bi-hexagon socket, 3/8 inch Width across flats 1/4 in	637100 1/4
Bi-hexagon socket, 3/8 inch Width across flats 11/16 in	637100 11/16
Bi-hexagon socket, 3/8 inch Width across flats 8 mm	637000 8