



Socket set 3/8 inch square drive 33 pieces metric / imperial



Order data

| | |
|--------------|---------------|
| Order number | 634711 |
| GTIN | 4018754260430 |
| Item class | 63A |

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For hexagon head screws / nuts with thread M4 – M14, for nuts / bolts with thread up to 9/16 inch (American inch sizes).

Material:

Chrome alloy steel, chrome-plated.

Supplied with:

Bi-hexagon sockets: 16 pcs. No. 637000

size 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22

Bi-hexagon sockets: 12 pcs. No. 637100 size 1/4; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4; 13/16; 7/8

T-handle: 1 pc. No. 635700

Extensions: 2 pcs. No. 63 5400 size 75; 240 mm

Universal joint: 1 pc. No. 636200

Ratchet: 1 pc. No. 635000

Presented in: ABS plastic box

Height: 57 mm

Square drive: 3/8 inch

Width across flats range, bi-hex sockets: 7-22 mm

Width across flats range, bi-hex sockets: 1/4-7/8 inch

Technical description

| | |
|--|-------------------|
| Width across flats range, bi-hex sockets | 7-22 mm |
| Width across flats range, bi-hex sockets | 1/4-7/8 inch |
| Width across flats | metric / imperial |
| Square drive | 3/8 inch |
| Number of pieces | 33 |
| Drive profile | Bi-hex socket |
| Length | 413 mm |
| Width | 230 mm |
| Height | 57 mm |
| Type of product | Socket spanner |

Accessories

| | |
|---|--------------|
| Bi-hexagon socket, 3/8 inch Width across flats 18 mm | 637000 18 |
| Bi-hexagon socket, 3/8 inch Width across flats 3/8 inch | 637100 3/8 |
| Bi-hexagon socket, 3/8 inch Width across flats 7/16 inch | 637100 7/16 |
| Bi-hexagon socket, 3/8 inch Width across flats 13 mm | 637000 13 |
| Bi-hexagon socket, 3/8 inch Width across flats 11/32 inch | 637100 11/32 |
| Bi-hexagon socket, 3/8 inch Width across flats 9/16 inch | 637100 9/16 |
| Bi-hexagon socket, 3/8 inch Width across flats 5/16 inch | 637100 5/16 |
| Bi-hexagon socket, 3/8 inch Width across flats 9 mm | 637000 9 |
| Extension, 3/8 inch overall length 240 mm | 635400 240 |
| Bi-hexagon socket, 3/8 inch Width across flats 15 mm | 637000 15 |
| Universal joint, 3/8 inch Type 3/8 | 636200 3/8 |
| T-handle, 3/8 inch overall length 165 mm | 635700 165 |
| Bi-hexagon socket, 3/8 inch Width across flats 20 mm | 637000 20 |
| Bi-hexagon socket, 3/8 inch Width across flats 7 mm | 637000 7 |
| Extension, 3/8 inch overall length 75 mm | 635400 75 |

| | |
|---|--------------|
| Bi-hexagon socket, 3/8 inch Width across flats 11 mm | 637000 11 |
| Bi-hexagon socket, 3/8 inch Width across flats 17 mm | 637000 17 |
| Bi-hexagon socket, 3/8 inch Width across flats 3/4 inch | 637100 3/4 |
| Bi-hexagon socket, 3/8 inch Width across flats 5/8 inch | 637100 5/8 |
| Bi-hexagon socket, 3/8 inch Width across flats 19 mm | 637000 19 |
| Bi-hexagon socket, 3/8 inch Width across flats 16 mm | 637000 16 |
| Bi-hexagon socket, 3/8 inch Width across flats 12 mm | 637000 12 |
| Reversible ratchet, 3/8 inch Type | 635000 |
| Bi-hexagon socket, 3/8 inch Width across flats 14 mm | 637000 14 |
| Bi-hexagon socket, 3/8 inch Width across flats 1/2 inch | 637100 1/2 |
| Bi-hexagon socket, 3/8 inch Width across flats 10 mm | 637000 10 |
| Bi-hexagon socket, 3/8 inch Width across flats 21 mm | 637000 21 |
| Bi-hexagon socket, 3/8 inch Width across flats 22 mm | 637000 22 |
| Bi-hexagon socket, 3/8 inch Width across flats 1/4 inch | 637100 1/4 |
| Bi-hexagon socket, 3/8 inch Width across flats 11/16 inch | 637100 11/16 |
| Bi-hexagon socket, 3/8 inch Width across flats 8 mm | 637000 8 |