



BiTorsion set of bits 61 pieces



Order data

Order number	675950
GTIN	4013288179937
Item class	63H

Description

Content:

Bits C 6.3 (1/4 inch) set; 1 coupling shank.

Content:

Bits, length 25 mm, C 6.3 for Phillips: No. 675510 1 pc. size 1/25; 2 pcs. size 2/25; 1 pc. size 3/25

Bits, length 25 mm, C 6.3 for Phillips: No. 675520 2 pcs. size 1/25; 8 pcs. size 2/25; 1 pc. size 3/25

Bits, length 25 mm, C 6.3 for Pozidriv: No. 675530 1 pc. size 1/25; 2 pcs. size 2/25; 1 pc. size 3/25

Bits, length 25 mm, C 6.3 for Pozidriv: 2 pcs. size 1; 8 pcs. size 2; 1 pc. size 3

Bits, length 25 mm, C 6.3 for hex socket: 3 pcs. size 2.5; 3 pcs. size 3.0; 3 pcs. size 4.0; 2 pcs. size 5.0

Bits, length 25 mm, C 6.3 for internal Torx®: No. 675550 3 pcs. size TX10; 2 pcs. size TX15; 4 pcs.

size TX20; 4 pcs. size TX25; 2 pcs. size TX30; 1 pc. size TX40

Bits, length 25 mm, C 6.3 for slot-head: 1 pc. each size 0.8×5.5; 1.0×5.5; 1.2×6.5

“Rapidaptor” adaptor: 1 pc. No. 675020 size 6.3K

Technical description

Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for Phillips

Drive profile	Pozidriv screwdriver
Manufacturer's designation	Bit-Safe 61 BiTorsion 1
Bit length	25 mm
Number of pieces	61
Colour coding	yes
Type of product	Bit tool

Accessories

Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Bit for Pozidriv, 1/4 inch C 6.3BiTorsion, diamond-coated Cross-head size / overall length 1/25 mm	675530 1/25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX20	675550 TX20
Bit for Phillips, 1/4 inch C 6.3BiTorsion diamond-coated Cross-head size / overall length 2/25 mm	675510 2/25
Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size / overall length 2/25 mm	675520 2/25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX15	675550 TX15
Bit for Pozidriv, 1/4 inch C 6.3BiTorsion, diamond-coated Cross-head size / overall length 2/25 mm	675530 2/25
Bit for Pozidriv, 1/4 inch C 6.3BiTorsion, diamond-coated Cross-head size / overall length 3/25 mm	675530 3/25
Bit for Phillips, 1/4 inch C 6.3BiTorsion diamond-coated Cross-head size / overall length 3/25 mm	675510 3/25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX30	675550 TX30
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX40	675550 TX40
Bit for Phillips, 1/4 inch C 6.3BiTorsion diamond-coated Cross-head size / overall length 1/25 mm	675510 1/25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX10	675550 TX10
Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size / overall length 3/25 mm	675520 3/25

Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size /
overall length 1/25 mm

675520 1/25

Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX25

675550 TX25