



Set of bits BiTorsion 30 pieces



Order data

Order number	675798
GTIN	4013288179821
Item class	63H

Description

Content:

Bits C 6.3 (1/4 inch) set; 1 coupling shank.

Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675520 2 pcs. size 1/25; 5 pcs. size 2/25; 2 pcs. size 3/25
 Bits, length 25 mm, C 6.3, for Pozidriv: No. 675540 2 pcs. size 1/25; 6 pcs. size 2/25; 2 pcs. size 3/25
 Bits, length 25 mm, C 6.3, for internal Torx®: No. 675550 1 pc. size TX10; 2 pcs. size TX15; 2 pcs. size TX20; 2 pcs. size TX25; 2 pcs. size TX30; 1 pc. size TX40

"Rapidaptor" adaptor: 1 pc. No. 675020 size 6.3K

Bit length: 25 mm

Technical description

Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Hexagon screwdriver
Manufacturer's designation	Bit-Check 30 BiTorsion 1
Bit length	25 mm

Number of pieces	30
Type of product	Bit tool

Accessories

Bit for Pozidriv, 1/4 inch BiTorsion Cross-head size / overall length 2/25 mm	675540 2/25
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX30	675550 TX30
Bit for Phillips, 1/4 inch BiTorsion Cross-head size / overall length 1/25 mm	675520 1/25
Bit for Pozidriv, 1/4 inch BiTorsion Cross-head size / overall length 3/25 mm	675540 3/25
Bit for Phillips, 1/4 inch BiTorsion Cross-head size / overall length 2/25 mm	675520 2/25
Bit for Phillips, 1/4 inch BiTorsion Cross-head size / overall length 3/25 mm	675520 3/25
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX40	675550 TX40
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX15	675550 TX15
Bit for Pozidriv, 1/4 inch BiTorsion Cross-head size / overall length 1/25 mm	675540 1/25
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX25	675550 TX25
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX10	675550 TX10
Bit for Torx®, 1/4 inch BiTorsion Torx® profile TX20	675550 TX20