



## Set of bits Metal 30 pieces



### Order data

Order number	675793
GTIN	4013288179838
Item class	63H

### Description

#### Content:

Bits C 6.3 (1/4 inch) set; 1 coupling shank.

#### Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675310 3 pcs. size 1/25; 3 pcs. size 2/25; 2 pcs. size 3/25

Bits, length 25 mm, C 6.3, for Pozidriv: No. 675320 3 pcs. size 1/25; 3 pcs. size 2/25; 3 pcs. size 3/25

Bits, length 25 mm, C 6.3, for hex socket: No. 675240 1 pc. each size 4; 5; 6

Bits, length 25 mm, C 6.3, for internal Torx®: No. 675340 1 pc. each size TX10; TX15; TX20; TX25;

TX30; TX40

Bits, length 25 mm, C 6.3, for slot-head: 1 pc. each size 0.6x4.5; 1.0x5.5; 1.2x6.5

Adapter: 1 pc.

### Technical description

Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Manufacturer's designation	Bit-Check 30 Metal 1

Number of pieces	30
Type of product	Bit tool

## Accessories

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm	675240 6
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX15	675340 TX15
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675310 2/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX20	675340 TX20
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675310 1/25
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675320 3/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX40	675340 TX40
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm	675240 4
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675340 TX25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX30	675340 TX30
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX10	675340 TX10
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm	675240 5
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675320 2/25
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675310 3/25
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675320 1/25