



Socket set for Torx®, 1/4; 3/8; 1/2 inch square drive 34 pieces



Order data

Order number	630031
GTIN	4018754261017
Item class	63A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For external Torx® screws with thread M3 – M20. For internal Torx® screws with thread M2.5 – M14.

For internal Torx® screws with retaining pin with thread M3 – M8.

Material:

Chrome alloy steel, chrome-plated.

Supplied with:

1/4 inch sockets for Torx®: 3 pcs. No. 631500 size E4; E5; E6

3/8 inch sockets for Torx®: 4 pcs. No. 637450 size E7; E8; E10; E12

1/2 inch sockets for Torx®: 6 pcs. No. 642700 size E11; E14; E16; E18; E20; E24

1/4 inch bits for Torx®: 2 pcs. No. 631801 size TX8; TX9

3/8 inch bits for Torx®: 5 pcs. No. 637560 size TX10; TX15; TX20; TX25; TX27

1/2 inch bits for Torx®: 6 pcs. No. 643650 size TX30; TX40; TX45; TX50; TX55; TX60

Bits with bore for Torx®, C 6.3: 7 pcs. similar to No. 675350 size TX10; TX15; TX20; TX25; TX27; TX30; TX40

Bit adapter: 1 pc. similar to No. 676945 size 8/4

Presented in: ABS plastic box

Technical description

Drive profile	Screwdriver for TORX® screws with hole
Drive profile	Screwdriver for TORX® screws
Drive profile	Socket for TORX® screws
Square drive	1/4 in
Square drive	1/2 in
Square drive	3/8 in
Number of pieces	34
Packaging	ABS plastic box
Length	413 mm
Width	230 mm
Height	57 mm
Type of product	Socket insert

Accessories

Socket, 1/4 inch for Torx® Torx® profile E4	631500 E4
Socket, 1/4 inch for Torx® Torx® profile E5	631500 E5
Socket, 1/4 inch for Torx® Torx® profile E6	631500 E6
Bit socket for Torx®, 1/4 inchshort Torx® profile TX8	631801 TX8
Bit socket for Torx®, 1/4 inchshort Torx® profile TX9	631801 TX9
Socket, 3/8 inch for Torx® Torx® profile E10	637450 E10
Socket, 3/8 inch for Torx® Torx® profile E12	637450 E12
Socket, 3/8 inch for Torx® Torx® profile E7	637450 E7
Socket, 3/8 inch for Torx® Torx® profile E8	637450 E8
Bit socket, for Torx®, 3/8 inchshort Torx® profile TX10	637560 TX10
Bit socket, for Torx®, 3/8 inchshort Torx® profile TX15	637560 TX15
Bit socket, for Torx®, 3/8 inchshort Torx® profile TX20	637560 TX20
Bit socket, for Torx®, 3/8 inchshort Torx® profile TX25	637560 TX25

Bit socket, for Torx®, 3/8 inch short Torx® profile TX27	637560 TX27
Socket, 1/2 inch for Torx® Torx® profile E11	642700 E11
Socket, 1/2 inch for Torx® Torx® profile E14	642700 E14
Socket, 1/2 inch for Torx® Torx® profile E16	642700 E16
Socket, 1/2 inch for Torx® Torx® profile E18	642700 E18
Socket, 1/2 inch for Torx® Torx® profile E20	642700 E20
Socket, 1/2 inch for Torx® Torx® profile E24	642700 E24
Bit socket, for Torx®, 1/2 inch Torx® profile TX30	643650 TX30
Bit socket, for Torx®, 1/2 inch Torx® profile TX40	643650 TX40
Bit socket, for Torx®, 1/2 inch Torx® profile TX45	643650 TX45
Bit socket, for Torx®, 1/2 inch Torx® profile TX50	643650 TX50
Bit socket, for Torx®, 1/2 inch Torx® profile TX55	643650 TX55
Bit socket, for Torx®, 1/2 inch Torx® profile TX60	643650 TX60