



Bit set with drive tool and hexagon key L-wrenches 52 pieces



Order data

Order number	675990
GTIN	4013288179968
Item class	63H

Description

Version:

Kraftform handle with quick-change holder for 1/4 inch bits with C 6.3 and E 6.3 shank. Including hexagon key L-wrenches with ball-point in the sizes 1.5 – 8.0 mm.

Practical Kraftform Kompakt® set of bits and drive tool **for manual and machine drives**.

Supplied in a sturdy textile tool roll with hook and loop fastener.

Advantage:

Colour-coding and numerical marking ensure easy identification of bits.

Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675520 2 pcs. size 1/25; 4 pcs. size 2/25; 2 pcs. size 3/25

Bits, length 25 mm, C 6.3, for Pozidriv: 2 pcs. size 1; 4 pcs. size 2; 2 pcs. size 3

Bits, length 25 mm, C 6.3, for internal Torx®: No. 675550 2 pcs. size TX10; 2 pcs. size TX15; 3 pcs. size TX20; 2 pcs. size TX25; 2 pcs. size TX30; 1 pc. size TX40

Bits, length 25 mm, C 6.3, for slot-head: 1 pcs. each size 0.8x5.5; 1.0x5.5

IMPACTOR bits, length 50 mm, E 6.3, for Phillips: 2 pc. size 2; 1 pc. size 3

IMPACTOR bits, length 50 mm, E 6.3, for Pozidriv: 2 pc. size 2; 1 pc. size 3

IMPACTOR bits, length 50 mm, E 6.3, for hex socket: 1 pc. each size 4; 5; 6

IMPACTOR bits, length 50 mm, E 6.3, for internal Torx®: 1 pc. each size TX25; TX30; TX40

L-wrench with ball point Hex-Plus, for hex socket: 1 pc. each size 1.5; 2.0; 2.5; 3.0; 4.0; 5.0; 6.0; 8.0 mm

Screwdriver handle: 1 pc.

"Rapidaptor" adaptor: 1 pc. No. 675020 size 6.3K

Technical description

Bit hexagon shank	C 6,3
Bit hexagon shank	E 6,3
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Hexagon screwdriver
Manufacturer's designation	Kraftform Kompakt 100
Number of pieces	52
Drive tool	Screwdriver handle with quick-change holder
suitable for machine	yes
Type of product	Bit tool

Accessories

Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX15	675550 TX15
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX10	675550 TX10
Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size / overall length 2/25 mm	675520 2/25
Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size / overall length 3/25 mm	675520 3/25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX30	675550 TX30
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
IMPAKTOR bit for Pozidriv, 1/4 inch E 6.3 Cross-head size 3	674122 3
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX25	675550 TX25
Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX40	675550 TX40
	675520 1/25

Bit for Phillips, 1/4 inch C 6.3BiTorsion Cross-head size /
overall length 1/25 mm

Bit for Torx®, 1/4 inch C 6.3BiTorsion Torx® profile TX20

675550 TX20