

Garant**Set of parallels, Length: 100mm****Order data**

Order number	366702 100
GTIN	4045197799166
Item class	31Z

Description**Version:**

GARANT – **precision version**. Pairing tolerance ≤ 0.004 mm, width / height tolerance ≤ 0.007 mm, extremely precise flatness and rectangularity. Parallels stored in special plastic stand.

Hardness: 60 HRC.

Precision ground as pairs.**Application:**

In high precision work for parallel mounting of components in machine vices or jigs.

Content:

2×5; 2×10; 2×15; 2×20; 3×6;
3×11; 3×16; 3×21; 4×7; 4×12;
4×17; 4×22; 5×8; 5×13; 5×18;
5×23; 6×9; 6×14; 6×19; 6×24

Note:

Sizes 125 – 200: In 1 mm increments, except 9 mm, all other dimensions achievable.

See the spare parts list for spare holders.

Technical description

Length	100 mm
--------	--------

Number of strips	20 pair
Shape description	flat
Shape description	parallel
Shape description	rectangular
Type of product	Pairs of parallels

Accessories

Single pair of parallels for 366702 / 6704 size 100 Width×height 3X16 mm	366706 3X16
Single pair of parallels for 366702 / 6704 size 100 Width×height 5X13 mm	366706 5X13
Single pair of parallels for 366702 / 6704 size 100 Width×height 5X8 mm	366706 5X8
Single pair of parallels for 366702 / 6704 size 100 Width×height 6X19 mm	366706 6X19
Single pair of parallels for 366702 / 6704 size 100 Width×height 3X6 mm	366706 3X6
Single pair of parallels for 366702 / 6704 size 100 Width×height 6X9 mm	366706 6X9
Single pair of parallels for 366702 / 6704 size 100 Width×height 3X21 mm	366706 3X21
Single pair of parallels for 366702 / 6704 size 100 Width×height 2X15 mm	366706 2X15
Single pair of parallels for 366702 / 6704 size 100 Width×height 4X7 mm	366706 4X7
Single pair of parallels for 366702 / 6704 size 100 Width×height 2X20 mm	366706 2X20
Single pair of parallels for 366702 / 6704 size 100 Width×height 6X24 mm	366706 6X24
Plastic stand for parallels Type 100	366701 100
Single pair of parallels for 366702 / 6704 size 100 Width×height 2X5 mm	366706 2X5

Single pair of parallels for 366702 / 6704 size 100 Width×height 4X17 mm	366706 4X17
Single pair of parallels for 366702 / 6704 size 100 Width×height 5X18 mm	366706 5X18
Single pair of parallels for 366702 / 6704 size 100 Width×height 2X10 mm	366706 2X10
Single pair of parallels for 366702 / 6704 size 100 Width×height 3X11 mm	366706 3X11
Single pair of parallels for 366702 / 6704 size 100 Width×height 5X23 mm	366706 5X23
Single pair of parallels for 366702 / 6704 size 100 Width×height 4X12 mm	366706 4X12
Single pair of parallels for 366702 / 6704 size 100 Width×height 4X22 mm	366706 4X22
Single pair of parallels for 366702 / 6704 size 100 Width×height 6X14 mm	366706 6X14