

Garant**Set of parallels, Length: 200mm****Order data**

Order number	366702 200
GTIN	4045197799302
Item class	31Z

Description**Version:**

GARANT – **precision version**. Pairing tolerance ≤ 0.004 mm, width / height tolerance ≤ 0.007 mm, extremely precise flatness and rectangularity. Parallels stored in special plastic stand. Hardness: 60 HRC.

Precision ground as pairs.**Application:**

In high precision work for parallel mounting of components in machine vices or jigs.

Content:

8×11; 8×16; 8×21; 8×26; 8×31; 8×36;
10×13; 10×18; 10×23; 10×28; 10×33; 10×38;
12×15; 12×20; 12×25; 12×30; 12×35; 12×40;
14×17; 14×22; 14×27; 14×32; 14×37; 14×42

Note:

Sizes 125 – 200: In 1 mm increments, except 9 mm, all other dimensions achievable. See the spare parts list for spare holders. In 1 mm increments (except 9 mm), all other dimensions achievable.

Technical description

Length	200 mm
Number of strips	24 pair

Shape description	flat
Shape description	parallel
Shape description	rectangular
Type of product	Pairs of parallels

Accessories

Single pair of parallels for 366702 size 200 Width×height 14X27 mm	366726 14X27
Single pair of parallels for 366702 size 200 Width×height 12X40 mm	366726 12X40
Single pair of parallels for 366702 size 200 Width×height 12X35 mm	366726 12X35
Single pair of parallels for 366702 size 200 Width×height 8X31 mm	366726 8X31
Single pair of parallels for 366702 size 200 Width×height 8X11 mm	366726 8X11
Single pair of parallels for 366702 size 200 Width×height 12X15 mm	366726 12X15
Single pair of parallels for 366702 size 200 Width×height 10X33 mm	366726 10X33
Single pair of parallels for 366702 size 200 Width×height 10X38 mm	366726 10X38
Single pair of parallels for 366702 size 200 Width×height 8X26 mm	366726 8X26
Single pair of parallels for 366702 size 200 Width×height 10X13 mm	366726 10X13
Single pair of parallels for 366702 size 200 Width×height 8X16 mm	366726 8X16
Single pair of parallels for 366702 size 200 Width×height 10X23 mm	366726 10X23
Single pair of parallels for 366702 size 200 Width×height 8X21 mm	366726 8X21

Single pair of parallels for 366702 size 200 Width×height 14X22 mm	366726 14X22
Single pair of parallels for 366702 size 200 Width×height 14X32 mm	366726 14X32
Single pair of parallels for 366702 size 200 Width×height 10X18 mm	366726 10X18
Plastic stand for parallels Type 125-200	366701 125-200
Single pair of parallels for 366702 size 200 Width×height 10X28 mm	366726 10X28
Single pair of parallels for 366702 size 200 Width×height 12X25 mm	366726 12X25
Single pair of parallels for 366702 size 200 Width×height 8X36 mm	366726 8X36
Single pair of parallels for 366702 size 200 Width×height 14X42 mm	366726 14X42
Single pair of parallels for 366702 size 200 Width×height 14X37 mm	366726 14X37
Single pair of parallels for 366702 size 200 Width×height 12X20 mm	366726 12X20
Single pair of parallels for 366702 size 200 Width×height 14X17 mm	366726 14X17
Single pair of parallels for 366702 size 200 Width×height 12X30 mm	366726 12X30