

Garant**Double-ended ring spanner set, deeply cranked, Number of keys: 13****Order data**

Order number	615610 13
GTIN	4062406221133
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

Standard:

DIN 838 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34; 36×41

Note:

HT-Drive – the particularly close-fitting profile.

Advantage

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Technical description

Width across flats	metric
--------------------	--------

Number of keys	13
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	matt chrome-plated
Measurement system metric	yes
Measurement system imperial	no
Ring end deep cranked	no
Type of product	Spanner

Accessories

Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615600 16X17
Double-ended ring spanner, deeply cranked Width across flats 27X32 mm	615600 27X32
Double-ended ring spanner, deeply cranked Width across flats 36X41 mm	615600 36X41
Double-ended ring spanner, deeply cranked Width across flats 21X23 mm	615600 21X23
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615600 10X11
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615600 8X9
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615600 12X13
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615600 14X15
Double-ended ring spanner, deeply cranked Width across flats 20X22 mm	615600 20X22
Double-ended ring spanner, deeply cranked Width across flats 24X26 mm	615600 24X26

Double-ended ring spanner, deeply cranked Width across flats 6X7 mm

615600 6X7

Double-ended ring spanner, deeply cranked Width across flats 18X19 mm

615600 18X19

Double-ended ring spanner, deeply cranked Width across flats 30X34 mm

615600 30X34