



Socket set 1/4 inch square drive 29 pieces, Type: 6



Order data

Order number	630368 6
GTIN	4062406230203
Item class	62A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For external hexagon screws / nuts with thread M2 – M8

and for hexagon socket head screws with thread M4 – M8.

For Phillips screws with thread M2 – M6 and for slot-head screws with thread M2.5 – M5.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets single hexagon: 12 pcs. No. 631020 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13

Hexagon screwdriver bits: 4 pcs. No. 631720 size 3; 4; 5; 6

Bits, C 6.3, for Phillips: 3 pcs. similar to No. 675200 size 1, 2; 3

Bits, C 6.3, for slot-head: 3 pcs. similar to No. 675250 size 4, 5.5; 8

Holder for bits: 1 pc. No. 676800 size 4/4

T-handle: 1 pc. similar to No. 633029

Spin type speeder: 1 pc. No. 632840 size 150

Extensions: 1 pc. 75 mm

1 pc. No. 632420 size 150

Universal joint: 1 pc. No. 633520 size 1/4

Ratchet: 1 pc. No. 632090 size 1/4

Storage in: ABS plastic box

Technical description

Square drive	1/4 in
Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Hexagon screwdriver
Drive profile	Hexagon socket
Number of pieces	29
Width across flats range, hexagon sockets	4-13 mm
Width across flats range, hexagon wrenches	3-6 mm
Packaging	ABS plastic box
Length	257 mm
Width	149 mm
Height	47 mm
Type of product	Socket spanner

Accessories

Bit for slot-head, 1/4 inch C 6.3 Blade width 5,5 mm	675250 5,5
Bit for slot-head, 1/4 inch C 6.3 Blade width 8 mm	675250 8
Adapter Type 4/4	676800 4/4
Extension, 1/4 inch overall length 150 mm	632420 150
Hexagon socket, 1/4 inch Width across flats 11 mm	631020 11
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm	675200 3/25
Hexagon socket, 1/4 inch Width across flats 10 mm	631020 10
Bit for slot-head, 1/4 inch C 6.3 Blade width 4 mm	675250 4
Hexagon socket, 1/4 inch Width across flats 8 mm	631020 8
Spinner handle, 1/4 inch overall length 150	632840 150
Rigid foam inlay for set 630368	630324 630368

Hexagon socket, 1/4 inch Width across flats 13 mm	631020 13
Hexagon bit socket, 1/4 inchshort Hexagon 5 mm	631720 5
Hexagon bit socket, 1/4 inchshort Hexagon 4 mm	631720 4
Reversible ratchet, 1/4 inch with ejector Type 1/4	632090 1/4
Hexagon bit socket, 1/4 inchshort Hexagon 6 mm	631720 6
Hexagon socket, 1/4 inch Width across flats 12 mm	631020 12
Hexagon socket, 1/4 inch Width across flats 5 mm	631020 5
Universal joint 1/4 inch Type 1/4	633520 1/4
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm	675200 2/25
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631020 5,5
Hexagon socket, 1/4 inch Width across flats 4 mm	631020 4
Hexagon socket, 1/4 inch Width across flats 6 mm	631020 6
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm	675200 1/25
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631020 4,5
Hexagon bit socket, 1/4 inchshort Hexagon 3 mm	631720 3
Hexagon socket, 1/4 inch Width across flats 7 mm	631020 7
Hexagon socket, 1/4 inch Width across flats 9 mm	631020 9
T-handle, 1/4 inch overall length 116 mm	633029 116
Modular box Type 2	630323 2