


ESD basic installation set, Number of tools: 15



Order data

Order number	973235 15
GTIN	2050002041943
Item class	91A

Description

Version:

Popular tool selections in ESD foam inlay. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

ESD rigid foam inlay, empty No. 973200 size 973235: 1 pc.

PB SWISS TOOLS ESD screwdriver for slot-head No. 660050 size 2.5; 3.5; 4; 5.5; 6.5: 1 pc. each

PB SWISS TOOLS ESD screwdriver for Pozidriv No. 667687 size 1; 2: 1 pc. each

GARANT ESD electronics side cutter No. 726210 size 125: 1 pc.

GARANT ESD electronics side cutter, pointed head No. 726250 size 125: 1 pc.

GARANT ESD electronics snipe-nosed pliers No. 727170 size 140: 1 pc.

HOLEX ESD tweezers, pointed tips, No. 727510 size AMB: 1 pc.

HOLEX ESD tweezers, angled tips, No. 727600 size AMB: 1 pc.

GARANT easyPick ESD small parts storage bin No. 972312 size 3x3/1: 3 pcs.

Technical description

Number of tools	15
Depth in G	20
Depth	500 mm
Width	300 mm

Width in G	12
Version	with tool kit
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	12×20
electrostatic characteristic	EGB/ESD
Type of product	Rigid foam inlay

Accessories

Rigid foam inlay, empty, for tool setsESD suitable for rigid foam set 973235	973200 973235
Electronics side cutter, standard head shape Overall length 125 mm	726210 125
Screwdriver for Pozidriv, with 2-component SwissGrip handleESD Cross-head size 1	667687 1
Tweezers pointed, 115 mm Form 3c Material AMB	727510 AMB
Electronics side cutter, pointed head Overall length 125 mm	726250 125
Screwdriver for slot-head, with 2-component SwissGrip handleESD Blade width b 5,5 mm	660050 5,5
Tweezers with narrow tips angled, 150 mm, Form 22b Material AMB	727600 AMB
Screwdriver for slot-head, with 2-component SwissGrip handleESD Blade width b 3,5 mm	660050 3,5
Screwdriver for slot-head, with 2-component SwissGrip handleESD Blade width b 4 mm	660050 4
Screwdriver for slot-head, with 2-component SwissGrip handleESD Blade width b 2,5 mm	660050 2,5
ESD small parts storage bin Height mm / type 26/1	972310 26/1
Electronics snipe-nosed pliers Overall length 140 mm	727170 140
Screwdriver for slot-head, with 2-component SwissGrip handleESD Blade width b 6,5 mm	660050 6,5

Screwdriver for Pozidriv, with 2-component SwissGrip
handleESD Cross-head size 2

667687 2