



Cordless impact wrench / impact driver, Type: GDS18300



Order data

Order number	074052 GDS18300
GTIN	3165140984423
Item class	03B

Description

Version:

Cordless impact wrench / impact driver

- **Reversible.**
- **Battery charge display.**

Integral **Auto Bolt Release** (ABR Stop) automatically switches the tool off in anti-clockwise mode when required. Secure fixing and quick release of the socket, thanks to our new external square socket with snap ring and securing pin. With **ProCORE** 18V 4.0Ah battery.

Advantage:

Tightening torque of 300 Nm.

Supplied with:

Supplied with 2× Li-ion batteries, charger. L-BOXX.

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Packaging: Modular case (L-Boxx)

suitable battery - supplier / battery type / voltage: Bosch 18 V

Manufacturer's designation: GDS 18V-300

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 4 A·h

Battery voltage: 18 V

maximum screw \varnothing (8.8 - 12.9): M20

Technical description

Tool arbor size	1/2 in
Packaging	Modular case (L-Boxx)
typical application	Heavy Duty
maximum screw \varnothing (8.8 - 12.9)	M20
Tool arbor drive profile	External square drive
Battery voltage	18 V
maximum torque hard	300 N·m
suitable battery - supplier / battery type / voltage	Bosch 18 V
Weight	2.3 kg
maximum speed 1st speed	2400 min ⁻¹
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Battery capacity	4 A·h
maximum vibration to EN	12.5 m/s ²
Number of impacts	0 - 3400 min ⁻¹
Manufacturer's designation	GDS 18V-300
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion battery ProCore Battery type, battery voltage C18 V	073857 C18
Battery starter set ProCore Battery type, battery voltage C18 V	073865 C18
Li-ion battery Battery type, battery voltage B18 V	073851 B18
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery ProCore Battery type, battery voltage C18 V	073858 C18

Battery charger Type 1880CV	073866 1880CV
Li-ion battery ProCore Battery type, battery voltage C18 V	073856 C18
Battery starter set ProCore Battery type, battery voltage C18 V	073863 C18
Battery starter set ProCore Battery type, battery voltage C18 V	073867 C18