



## Bit set with turbo drive tool 19 pieces, Number of pieces: 19



### Order data

Order number	676205 19
GTIN	4013288214614
Item class	63H

### Description

#### Version:

Practical Kraftform Kompakt® set of bits and drive tool **for manual and machine drives**.

**Kraftform** handle with quick-change holder for 1/4 inch bits with C 6.3 **and** E 6.3 shank.

Up to **four screw tightening speeds** within a handle, optionally by the press of a button or a planetary gearbox that can be **engaged/disengaged**. Switching off is recommended before fine adjustment and the final tightening or release of a screw with a high torque (up to 14 Nm).

Kraftform handle with **Rapidaptor bit holder** for 1/4 inch bits with C 6.3 and E 6.3 shank.

Supplied in a sturdy textile tool roll with hook and loop fastener.

#### Advantage:

- **Powerful final tightening and simple fine adjustment.**
- **Purely mechanical 4-fold multiplication (without battery) of the screw speed.**

#### Content:

Bits, length 89 mm, E 6.3, for Phillips: 1 pc. each No. 674200 size 1/89; 2/89; 3/89

Bits, length 89 mm, E 6.3, for Pozidriv: 1 pc. each No. 674220 size 1/89; 2/89; 3/89

Bits, length 89 mm, E 6.3, for hex socket: 1 pc. each No. 674244 size 3; 4; 5; 6

Bits, length 89 mm, E 6.3, for inner Torx®: 1 pc. each No. 674250 size TX10/89; TX15/89; TX20/89; TX25/89; TX30/89

Bits, length 89 mm, E 6.3, for slot-head: 1 pc. size 0.8×4.0; 1.0×5.5; 1.2×6.5

Screwdriver handle: 1 pc. No. 676390

### Technical description

Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Hexagon screwdriver
Manufacturer's designation	Kraftform Kompakt Turbo 1
Drive tool	Screwdriver holder
Drive tool	1 bit ratchet, 1/4 inch
Drive tool	Nut ratchet, 1/4 inch
Type of product	Bit tool

## Accessories

Bit for Pozidriv, 1/4 inch E 6.3 Cross-head size / overall length 2/89 mm	674220 2/89
Turbo Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3 with quick-change chuck Hexagon socket 6,3	676390 6,3
Bit for Pozidriv, 1/4 inch E 6.3 Cross-head size / overall length 3/89 mm	674220 3/89
Bit for hexagon, long, 1/4 inch E 6.3 Hex-Plus profile with bore Hexagon 4 mm	674244 4
Bit for Phillips, 1/4 inch E 6.3 Cross-head size / overall length 3/89 mm	674200 3/89
Bit for Torx®, long, 1/4 inch E 6.3 Torx® profile / overall length TX20/89 mm	674250 TX20/89
Bit for hexagon, long, 1/4 inch E 6.3 Hex-Plus profile with bore Hexagon 3 mm	674244 3
Bit for Phillips, 1/4 inch E 6.3 Cross-head size / overall length 2/89 mm	674200 2/89
Bit for Torx®, long, 1/4 inch E 6.3 Torx® profile / overall length TX15/89 mm	674250 TX15/89
	674220 1/89

Bit for Pozidriv, 1/4 inch E 6.3 Cross-head size / overall length 1/89 mm

Bit for hexagon, long, 1/4 inch E 6.3 Hex-Plus profile with bore Hexagon 5 mm

674244 5

Bit for hexagon, long, 1/4 inch E 6.3 Hex-Plus profile with bore Hexagon 6 mm

674244 6

Bit for Torx®, long, 1/4 inch E 6.3 Torx® profile / overall length TX25/89 mm

674250 TX25/89

Bit for Torx®, long, 1/4 inch E 6.3 Torx® profile / overall length TX30/89 mm

674250 TX30/89

Bit for Phillips, 1/4 inch E 6.3 Cross-head size / overall length 1/89 mm

674200 1/89

Bit for Torx®, long, 1/4 inch E 6.3 Torx® profile / overall length TX10/89 mm

674250 TX10/89