

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 36×24G, Height mm / number of drawers: 800/5



Order data

Order number	931315 800/5
GTIN	4062406275563
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Fitted with:

Drawer front height, mm: 75, 100, 100, 125, 300

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer front height	75 mm
Drawer front height	100 mm

Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	300 mm
Number of drawers	5
Width	1000 mm
Usable height for drawers	700 mm
Drawer usable width in G	36
Depth	700 mm
Usable height	700 mm
Number of doors	0
Electronic locking system can be retrofitted	yes
Height	800 mm
Drawer usable depth in G	24
Drawer usable depth	600 mm
Weight	138 kg
Drawer usable area in G	36×24
Drawer usable width	900 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet

Accessories

Drawer,200 kg Drawer front height 75 mm	931355 75
Drawer,200 kg Drawer front height 300 mm	931355 300
Drawer,200 kg Drawer front height 150 mm	931355 150
Drawer,200 kg Drawer front height 200 mm	931355 200
Drawer,200 kg Drawer front height 100 mm	931355 100
Drawer,200 kg Drawer front height 125 mm	931355 125
Lock plate for GridLine Type HU21	914227 HU21
Drawer,200 kg Drawer front height 250 mm	931355 250
Tool cabinet casing for drawers Height 800 mm	931335 800