

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 36×24G, Height mm / number of drawers: 900/6A**Order data**

Order number	931305 900/6A
GTIN	4062406275549
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 75, 75, 150, 150, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Height	900 mm
Width	1000 mm

Weight	158 kg
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Number of drawers	6
Drawer usable width	900 mm
Drawer usable depth in G	24
Drawer usable depth	600 mm
Depth	700 mm
Electronic locking system can be retrofitted	yes
Usable height for drawers	800 mm
Number of doors	0
Drawer usable area in G	36×24
Usable height	800 mm
Drawer usable width in G	36
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet

Accessories

Drawer,75 kg Drawer front height 200 mm	931353 200
Drawer,75 kg Drawer front height 75 mm	931353 75
Drawer,75 kg Drawer front height 250 mm	931353 250
Drawer,75 kg Drawer front height 50 mm	931353 50
Drawer,75 kg Drawer front height 150 mm	931353 150
Drawer,75 kg Drawer front height 100 mm	931353 100
Drawer,75 kg Drawer front height 300 mm	931353 300
Drawer,75 kg Drawer front height 125 mm	931353 125
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 900 mm	931335 900