




Socket set 1/2 inch, Number of tools: 31



Order data

Order number	953831 31
GTIN	2050002042018
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 953831: 1 pc.

STAHLWILLE reversible ratchet, 1/2 inch No. 640100 size 1/2: 1 pc.

STAHLWILLE extension 1/2 inch No. 641000 size 75; 130; 255: 1 pc. each

STAHLWILLE T-handle 1/2 inch No. 641300 size 300: 1 pc.

STAHLWILLE universal joint 1/2 inch No. 641600 size 1/2: 1 pc.

STAHLWILLE bi-hex socket 1/2 inch No. 642100 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32: 1 pc. each

STAHLWILLE hexagon screwdriver bit 1/2 inch No. 643200 size 4; 5; 6; 7; 8; 10; 12; 14: 1 pc. each

Technical description

Depth in G	20
Width	250 mm
Depth	500 mm
Weight	4.142 kg
Width in G	10

Number of tools	31
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Square drive	1/2 in
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

Accessories

Bi-hexagon socket, 1/2 inch Width across flats 8 mm	642100 8
Bi-hexagon socket, 1/2 inch Width across flats 10 mm	642100 10
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642100 18
T-handle, 1/2 inch overall length 300 mm	641300 300
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643200 10
Universal joint, 1/2 inch Type 1/2	641600 1/2
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642100 24
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643200 12
Bi-hexagon socket, 1/2 inch Width across flats 30 mm	642100 30
Rigid foam inlay for tool sets suitable for rigid foam set 953831	952001 953831
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643200 4
Reversible ratchet, 1/2 inch Type 1/2	640100 1/2
Bi-hexagon socket, 1/2 inch Width across flats 12 mm	642100 12
Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642100 15
Bi-hexagon socket, 1/2 inch Width across flats 27 mm	642100 27
Extension, 1/2 inch overall length 255 mm	641000 255

Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643200 5
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642100 19
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642100 13
Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642100 17
Extension, 1/2 inch overall length 75 mm	641000 75
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642100 21
Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642100 14
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 7 mm	643200 7
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642100 22
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642100 16
Extension, 1/2 inch overall length 130 mm	641000 130
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643200 6
Bi-hexagon socket, 1/2 inch Width across flats 11 mm	642100 11
Bi-hexagon socket, 1/2 inch Width across flats 32 mm	642100 32
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643200 14
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643200 8