



Socket set 1/4 inch and 1/2 inch, Number of tools: 38



Order data

Order number	953829 38
GTIN	2050002042025
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay No. 952001 size 953829: 1 pc.

STAHLWILLE hexagon socket 1/4 inch No. 631000 size 4; 5; 5.5; 6; 7; 8; 9; 10; 11: 1 pc. each

STAHLWILLE hexagon screwdriver bit 1/4 inch No. 631700 size 3; 4; 5: 1 pc. each

STAHLWILLE reversible ratchet, 1/4 inch No. 632000 size 1/4: 1 pc.

STAHLWILLE extension 1/4 inch No. 632400 size 50; 150: 1 pc. each

STAHLWILLE spinner handle 1/4 inch No. 632800 size 150: 1 pc.

STAHLWILLE T-handle 1/4 inch alloy No. 633000 size 116: 1 pc.

STAHLWILLE universal joint 1/4 inch No. 633500 size 1/4: 1 pc.

STAHLWILLE reversible ratchet, 1/2 inch No. 640100 size 1/2: 1 pc.

STAHLWILLE extension 1/2 inch No. 641000 size 130; 255: 1 pc. each

STAHLWILLE T-handle 1/2 inch alloy No. 641300 size 300: 1 pc.

STAHLWILLE universal joint 1/2 inch alloy No. 641600 size 1/2: 1 pc.

STAHLWILLE bi-hex socket 1/2 inch No. 642200 size 13; 16; 17; 18; 19; 21; 22; 24; 27; 30: 1 pc. each

STAHLWILLE hexagon screwdriver bit 1/2 inch No. 643200 size 6; 8; 10; 12; 14: 1 pc. each

Technical description

Number of tools	38
-----------------	----

Depth	500 mm
Width in G	10
Weight	3.793 kg
Width	250 mm
Depth in G	20
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	10×20
Square drive	1/4 in
Square drive	1/2 in
Type of product	Rigid foam inlay

Accessories

Hexagon socket, 1/4 inch Width across flats 11 mm	631000 11
T-handle, 1/4 inch overall length 116 mm	633000 116
Screwdriver socket, hexagon, 1/4 inch long Hexagon 4 mm	631700 4
Reversible ratchet, 1/4 inch Type 1/4	632000 1/4
Hexagon socket, 1/4 inch Width across flats 5 mm	631000 5
Hexagon socket, 1/4 inch Width across flats 8 mm	631000 8
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643200 6
Extension, 1/2 inch overall length 255 mm	641000 255
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643200 10
Extension, 1/2 inch overall length 130 mm	641000 130
Hexagon socket, 1/2 inch Width across flats 27 mm	642200 27
Hexagon socket, 1/2 inch Width across flats 22 mm	642200 22
Hexagon socket, 1/2 inch Width across flats 18 mm	642200 18

Screwdriver socket, hexagon, 1/4 inch long Hexagon 3 mm	631700 3
Hexagon socket, 1/4 inch Width across flats 6 mm	631000 6
Hexagon socket, 1/2 inch Width across flats 17 mm	642200 17
Hexagon socket, 1/4 inch Width across flats 4 mm	631000 4
Hexagon socket, 1/4 inch Width across flats 9 mm	631000 9
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643200 8
Hexagon socket, 1/2 inch Width across flats 30 mm	642200 30
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631000 5,5
Screwdriver socket, hexagon, 1/4 inch long Hexagon 5 mm	631700 5
Extension, 1/4 inch overall length 50 mm	632400 50
Hexagon socket, 1/4 inch Width across flats 10 mm	631000 10
T-handle, 1/2 inch overall length 300 mm	641300 300
Spinner handle, 1/4 inch overall length 150 mm	632800 150
Hexagon socket, 1/2 inch Width across flats 19 mm	642200 19
Hexagon socket, 1/2 inch Width across flats 13 mm	642200 13
Hexagon socket, 1/2 inch Width across flats 21 mm	642200 21
Extension, 1/4 inch overall length 150 mm	632400 150
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643200 12
Reversible ratchet, 1/2 inch Type 1/2	640100 1/2
Hexagon socket, 1/2 inch Width across flats 24 mm	642200 24
Universal joint, 1/4 inch Type 1/4	633500 1/4
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643200 14
Hexagon socket, 1/2 inch Width across flats 16 mm	642200 16
Rigid foam inlay for tool sets suitable for rigid foam set 953829	952001 953829
Universal joint, 1/2 inch Type 1/2	641600 1/2
Hexagon socket, 1/4 inch Width across flats 7 mm	631000 7