



Socket set 1/4 inch square drive 38 pieces, Type: 38



Order data

Order number	630345 38
GTIN	4018754323241
Item class	63A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

Application:

For external hexagon screws / nuts with thread M2.5 – M8. For external Torx® with thread M3 – M8. For hexagon socket head screws with thread M4 – M8. For internal Torx® with thread M2.5 – M8.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Supplied with:

Sockets for bi-hexagon: 10 pcs. No. 630950 size 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13

Sockets for external Torx®: 6 pcs. No. 631500 size E4; E5; E6; E7; E8; E10

Screwdriver bits for Phillips: PH1; PH2

Screwdriver bits for hex socket: 5 pcs. No. 631710 size 3; 4; 5; 6; 8

Screwdriver bits for internal Torx®: 9 pcs. No. 631801 size TX8; TX9; TX10; TX15; TX20; TX25; TX27; TX30; TX40

QR T-handle: 1 pc. No. 633050 size 116

QR spinner handle: 1 pc. No. 632950 size 150

Extensions QR: 2 pcs. No. 632545 size 50; 150

Universal joint QR: 1 pc. No. 633550 size 1/4

Ratchet QR: 1 pc. No. 632355 size 1/4

Storage in: ABS plastic box

Technical description

Number of pieces	38
Width across flats range, bi-hex sockets	5-13 mm
Drive profile	Bi-hex socket
Drive profile	Socket for TORX® screws
Drive profile	Screwdriver for Phillips
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for TORX® screws
Square drive	1/4 in
Width across flats range, hexagon wrenches	3-8 mm
Width across flats	metric
Standard	DIN 3120
Standard	DIN 3122
Standard	DIN 3124
Material	Chrome alloy steel
Packaging	ABS plastic box
Length	227 mm
Width	131 mm
Height	57 mm
Surface	chrome plated (non-flaking)
with QuickRelease	yes
Type of product	Socket spanner

Accessories

Hexagon bit socket, 1/4 inchshort Hexagon 5 mm	631710 5
Bit socket for Torx®, 1/4 inchshort Torx® profile TX20	631801 TX20
Bi-hexagon socket, 1/4 inch Width across flats 13 mm	630950 13

Bi-hexagon socket, 1/4 inch Width across flats 10 mm	630950 10
Bit socket for Torx®, 1/4 inchshort Torx® profile TX25	631801 TX25
Extension, 1/4 inchQuickRelease overall length 50 mm	632545 50
Reversible precision ratchet, 1/4 inch with ejectorQuickRelease Type 1/4	632355 1/4
Bi-hexagon socket, 1/4 inch Width across flats 5,5 mm	630950 5,5
Hexagon bit socket, 1/4 inchshort Hexagon 3 mm	631710 3
T-handle, 1/4 inchQuickRelease overall length 116 mm	633050 116
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631000 5,5
Hexagon socket, 1/4 inch Width across flats 7 mm	631000 7
Socket, 1/4 inch for Torx® Torx® profile E8	631500 E8
Bit socket for Torx®, 1/4 inchshort Torx® profile TX30	631801 TX30
Bit socket for Torx®, 1/4 inchshort Torx® profile TX9	631801 TX9
Spinner handle, 1/4 inchQuickRelease overall length 150 mm	632950 150
Universal joint 1/4 inchQuickRelease Type 1/4	633550 1/4
Socket, 1/4 inch for Torx® Torx® profile E7	631500 E7
Extension, 1/4 inchQuickRelease overall length 150 mm	632545 150
Bi-hexagon socket, 1/4 inch Width across flats 11 mm	630950 11
Bit socket for Torx®, 1/4 inchshort Torx® profile TX8	631801 TX8
Hexagon bit socket, 1/4 inchshort Hexagon 6 mm	631710 6
Bi-hexagon socket, 1/4 inch Width across flats 8 mm	630950 8
Bit socket for Torx®, 1/4 inchshort Torx® profile TX15	631801 TX15
Bi-hexagon socket, 1/4 inch Width across flats 6 mm	630950 6
Hexagon socket, 1/4 inch Width across flats 13 mm	631000 13
Bit socket for Torx®, 1/4 inchshort Torx® profile TX10	631801 TX10
Bi-hexagon socket, 1/4 inch Width across flats 7 mm	630950 7
Bit socket for Torx®, 1/4 inchshort Torx® profile TX27	631801 TX27
Hexagon socket, 1/4 inch Width across flats 9 mm	631000 9
Socket, 1/4 inch for Torx® Torx® profile E10	631500 E10

Socket, 1/4 inch for Torx® Torx® profile E4	631500 E4
Hexagon socket, 1/4 inch Width across flats 6 mm	631000 6
Bi-hexagon socket, 1/4 inch Width across flats 5 mm	630950 5
Hexagon socket, 1/4 inch Width across flats 11 mm	631000 11
Hexagon bit socket, 1/4 inchshort Hexagon 8 mm	631710 8
Socket, 1/4 inch for Torx® Torx® profile E5	631500 E5
Bi-hexagon socket, 1/4 inch Width across flats 9 mm	630950 9
Bit socket for Torx® , 1/4 inchshort Torx® profile TX40	631801 TX40
Hexagon socket, 1/4 inch Width across flats 10 mm	631000 10
Hexagon socket, 1/4 inch Width across flats 12 mm	631000 12
Hexagon socket, 1/4 inch Width across flats 8 mm	631000 8
Bi-hexagon socket, 1/4 inch Width across flats 12 mm	630950 12
Socket, 1/4 inch for Torx® Torx® profile E6	631500 E6
Hexagon bit socket, 1/4 inchshort Hexagon 4 mm	631710 4