



Tool selection "Robust 45 Move" Electro 63 pieces, Number of tools: 63



Order data

Order number	680104 63
GTIN	4003773082606
Item class	73F

Description

Version:

Comprehensive electrician's tool kit in high-quality tool case. With mobility unit and telescopic handle.

Case made from polypropylene for the toughest operating conditions: Resistant to dust, watertight, and temperature resistant.

Supplied with:

Electrician's spirit level: 1 pc. No. 467415 size 430

Pocket spirit level electric: 1 pc. No. 467484 size 70

"JOKER" double-ended ring spanner: 1 pc. size 10×13 mm

Multi-function key TwinKey®: 1 pc. No. 623550

Socket set 1/4 inch, 28 pieces: 1 pc. No. 630295 size S

Screwdriver for Pozidriv, insulated to VDE: 1 pc. size 1

Screwdriver for slot-head, insulated to VDE: 1 pc. size 3.5 mm

Kraftform Kompakt VDE set, 16-piece: 1 pc. similar to No. 667260

Pointed combination pliers, chrome-plated, insulated to VDE: 1 pc. No. 701655 size 145

Water pump pliers Cobra® chemically blacked: 1 pc. No. 705800 size 180

Snipe nose pliers, angled, insulated to VDE: 1 pc. No. 713700 size 200

Heavy-duty side cutter, chrome-plated, insulated to VDE: 1 pc. No. 723500 size 200

Side cutters, chrome-plated, insulated to VDE: 1 pc. No. 725300 size 160

ErgoStrip® universal stripping tool: 1 pc. No. 728091 size 8-13
 Wire stripping tool up to 16 mm² Preci Strip: 1 pc. No. 728631 size 16
 Installation pliers, insulated to VDE: 1 pc. No. 728787 size 200
 Crimping tool for terminal sleeves up to 16 mm²: 1 pc.
 Electrician's chisel: 1 pc. No. 743000 size 250
 Engineer's hammer: 1 each size 300 g
 Pliers wrench: 1 pc. No. 813700 size 180
 Fixed blade cable knife, insulated to VDE: 1 pc. No. 844410
 Tool case: 1 pc. "Robust 45 Move"

Note:

Supplied with tools sorted in a tool case.

Technical description

Manufacturer's designation	Robust45 Move
Number of pieces	63
Type of product	tool set

Accessories

TwinKey® multi-function key	623550
Diagonal side cutter, chrome-platedVDE insulated overall length 160 mm	725300 160
Pliers wrench overall length 180 mm	813700 180
Kraftform Kompakt VDE set Number of pieces 18	667260 18
Cable knife fixedfully insulated to VDE	844410
Snipe-nose combination pliers, chrome-platedVDE insulated overall length 145 mm	701655 145
Socket set 1/4 inch square drive28 pieces Type S	630295 S
Diagonal side cutter, chrome-platedVDE insulated overall length 200 mm	723500 200
ErgoStrip® universal stripping tool for cable Ø 8-13 mm	728091 8-13
Pocket spirit levelElectric Length 70 mm	467484 70
Electrician's spirit level Length 430 mm	467415 430

Water pump pliers Cobra® chemically blacked overall length 180 mm	705800 180
Installation pliersVDE insulated overall length 200 mm	728787 200
Electrician's chisel overall length 250 mm	743000 250
Snipe nose pliers, angledVDE insulated overall length 200 mm	713700 200
PreciStrip 16 wire stripping tool for conductor cross-section 16 mm ²	728631 16