

Socket set 1/4 inch, Number of tools: 46



Order data

Order number	953743 46
GTIN	2050002075412
Item class	91A

Description

Version:

Popular tool sets in two-colour PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thereby indicating any missing tools.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Supplied with:

GARANT universal joint No. 633529 size 1/4: 1 pc.

HOLEX screwdriver bit for slot-head No. 631613 size 3.5; 4; 5.5; 8: 1 pc. each

GARANT socket for Torx® No. 631515 size E4; E5; E6; E7; E8; E10: 1 pc. each

GARANT extension No. 632429 size 50; 150: 1 pc. each

GARANT hexagon socket No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14: 1 pc. each

HOLEX screwdriver bit for Phillips No. 631623 size 1; 2; 3; 4: 1 pc. each

GARANT T-handle No. 633029 size 116: 1 pc.

GARANT reversible ratchet, No. 632025 size 1/4: 1 pc.

Rigid foam inlay, empty No. 952001 size 953743: 1 pc.

GARANT spinner handle No. 632829 size 146: 1 pc.

GARANT hexagon screwdriver bit No. 631729 size 2.5; 3; 4; 5; 6: 1 pc. each

HOLEX screwdriver bit for Torx®, long No. 631773 size TX8; TX9; TX10; TX15; TX20; TX25; TX30; TX40: 1 pc. each

Technical description

Depth	500 mm
Number of tools	46
Version	with socket
Width	200 mm
Depth in G	20
Width in G	8
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Square drive	1/4 in
Type of product	Rigid foam inlay

Accessories

Rigid foam inlay for tool sets suitable for rigid foam set 953743	952001 953743
Hexagon socket, 1/4 inchSurface Drive Width across flats 10 mm	631225 10
Hexagon socket, 1/4 inchSurface Drive Width across flats 11 mm	631225 11
Hexagon socket, 1/4 inchSurface Drive Width across flats 12 mm	631225 12
Hexagon socket, 1/4 inchSurface Drive Width across flats 13 mm	631225 13
Hexagon socket, 1/4 inchSurface Drive Width across flats 14 mm	631225 14
Hexagon socket, 1/4 inchSurface Drive Width across flats 4 mm	631225 4
Hexagon socket, 1/4 inchSurface Drive Width across flats 4,5 mm	631225 4,5
Hexagon socket, 1/4 inchSurface Drive Width across flats 5 mm	631225 5

Hexagon socket, 1/4 inchSurface Drive Width across flats 5,5 mm	631225 5,5
Hexagon socket, 1/4 inchSurface Drive Width across flats 6 mm	631225 6
Hexagon socket, 1/4 inchSurface Drive Width across flats 7 mm	631225 7
Hexagon socket, 1/4 inchSurface Drive Width across flats 8 mm	631225 8
Hexagon socket, 1/4 inchSurface Drive Width across flats 9 mm	631225 9
Socket, 1/4 inch for Torx® Torx® profile E10	631515 E10
Socket, 1/4 inch for Torx® Torx® profile E4	631515 E4
Socket, 1/4 inch for Torx® Torx® profile E5	631515 E5
Socket, 1/4 inch for Torx® Torx® profile E6	631515 E6
Socket, 1/4 inch for Torx® Torx® profile E7	631515 E7
Socket, 1/4 inch for Torx® Torx® profile E8	631515 E8
Bit for slot-head, 1/4 inch Blade width 3,5 mm	631613 3,5
Bit for slot-head, 1/4 inch Blade width 4 mm	631613 4
Bit for slot-head, 1/4 inch Blade width 5,5 mm	631613 5,5
Bit for slot-head, 1/4 inch Blade width 8 mm	631613 8
Screwdriver bit for Phillips, 1/4 inch Cross-head size 1	631623 1
Screwdriver bit for Phillips, 1/4 inch Cross-head size 2	631623 2
Screwdriver bit for Phillips, 1/4 inch Cross-head size 3	631623 3
Screwdriver bit for Phillips, 1/4 inch Cross-head size 4	631623 4
Screwdriver socket, hexagon, 1/4 inchlong Hexagon 2,5 mm	631729 2,5
Screwdriver socket, hexagon, 1/4 inchlong Hexagon 3 mm	631729 3
Screwdriver socket, hexagon, 1/4 inchlong Hexagon 4 mm	631729 4
Screwdriver socket, hexagon, 1/4 inchlong Hexagon 5 mm	631729 5
Screwdriver socket, hexagon, 1/4 inchlong Hexagon 6 mm	631729 6
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX10	631773 TX10

Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX15	631773 TX15
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX20	631773 TX20
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX25	631773 TX25
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX30	631773 TX30
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX40	631773 TX40
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX8	631773 TX8
Screwdriver bit for Torx®, 1/4 inchlong Torx® profile TX9	631773 TX9
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Extension, 1/4 inch overall length 150 mm	632429 150
Extension, 1/4 inch overall length 50 mm	632429 50
Spinner handle, 1/4 inch overall length 146 mm	632829 146
T-handle, 1/4 inch overall length 116 mm	633029 116
Universal joint 1/4 inch Type 1/4	633529 1/4