



Workshop set, Number of tools: 36



Order data

Order number	955018 36
GTIN	4067263934950
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Suitable for:

GARANT roller cabinets with full extension drawers and a drawer module of **20 G x 16 G** or 500 x 400 mm (W x D).

Roller cabinets No. 914520 – 914582.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955018: 1 pc.

HOLEX combination spanner No. 613950 size 5.5; 7; 8; 10; 13; 16; 17; 18; 19: 1 pc. each

HOLEX reversible ratchet, 1/2 inch No. 640190 size 1/2: 1 pc.

HOLEX extension 1/2 inch No. 641020 size 125; 250: 1 pc. each

HOLEX T-handle 1/2 inch No. 641320 size 295: 1 pc.

HOLEX universal joint 1/2 inch No. 641620 size 1/2: 1 pc.

HOLEX bi-hex socket 1/2 inch No. 642120 size 13; 14; 15; 16; 17; 18; 19; 21; 22; 24: 1 pc. each

HOLEX bi-hex socket long 1/8 inch No. 642520 size 17; 19; 21: 1 pc. each

HOLEX screwdriver for slot-head No. 660701 size 3.5; 5.5: 1 pc. each

HOLEX short screwdriver for slot-head No. 664201 size 5.5: 1 pc.

HOLEX screwdriver for Phillips No. 668401 size 1; 2: 1 pc. each

HOLEX stub screwdriver for Phillips No. 668471 size 2: 1 pc.

HOLEX combination pliers, vanadium No. 703000 size 180: 1 pc.

HOLEX water pump pliers No. 706151 size 250: 1 pc.

HOLEX engineer's hammer No. 750125 size 300: 1 pc.

Technical description

Depth	400 mm
Drawer usable area in G	20×16
Depth in G	16
Width	500 mm
Width in G	20
Version	for roller cabinet drawer
Rigid foam quality LD45, thickness	30 mm
Square drive	1/2 in
suitable for workstations and storage equipment	Roller cabinet
Type of product	Rigid foam inlay

Accessories

Combination spanner Width across flats 10 mm	613950 10
Combination spanner Width across flats 13 mm	613950 13
Combination spanner Width across flats 16 mm	613950 16
Combination spanner Width across flats 17 mm	613950 17
Combination spanner Width across flats 18 mm	613950 18
Combination spanner Width across flats 19 mm	613950 19
Combination spanner Width across flats 5,5 mm	613950 5,5
Combination spanner Width across flats 7 mm	613950 7
Combination spanner Width across flats 8 mm	613950 8
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Extension, 1/2 inch overall length 125 mm	641020 125

Extension, 1/2 inch overall length 250 mm	641020 250
T-handle, 1/2 inch overall length 295 mm	641320 295
Universal joint, 1/2 inch Type 1/2	641620 1/2
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642120 13
Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642120 14
Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642120 15
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642120 16
Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642120 17
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642120 18
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642120 19
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642120 21
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642120 22
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642120 24
Bi-hexagon socket deep, 1/2 inch Width across flats 17 mm	642520 17
Bi-hexagon socket deep, 1/2 inch Width across flats 19 mm	642520 19
Bi-hexagon socket deep, 1/2 inch Width across flats 21 mm	642520 21
Screwdriver for slot-head, with power grip Blade width b 3,5 mm	660701 3,5
Screwdriver for slot-head, with power grip Blade width b 5,5 mm	660701 5,5
Screwdriver for slot-head, short Blade width b 5,5 mm	664201 5,5
Screwdriver for Phillips, with power grip Cross-head size 1	668401 1
Screwdriver for Phillips, with power grip Cross-head size 2	668401 2
Screwdriver for Phillips, short Cross-head size 2	668471 2
Vanadium combination pliers, bright finished overall length 180 mm	703000 180
Water pump pliers with plastic coating Overall length 250 mm	706151 250
Engineer's hammer Weight without handle 300 g	750125 300
Rigid foam inlay for tool sets suitable for rigid foam set 955018	952001 955018

