



Tool Rebel roller cabinet with tool selection 9700, 94 pieces, Type: 1



Order data

Order number	689200 1
GTIN	4000896249183
Item class	66H

Description

Version:

Roller cabinet in exclusive Tool Rebel design with 7 drawers (5 shallow, 2 tall). The 2 upper shallow drawers are equipped with a high-quality 94-piece professional tool selection consisting of the following configuration: Screwdrivers, 1/4-inch sockets, combination spanners and L-keys. The contents of the other 5 drawers can be individually selected.

The general-purpose tool selection fits precisely in two-tone PE rigid foam inlays, in which each tool has its own defined place in the roller cabinet. The large storage and working area is made of solvent-resistant plastic and is completely sealed. The central locking mechanism is locked by a cylinder lock at the side. The oil-resistant and acid-resistant wheels can each be loaded with 250 kg and have precision ball bearings and a double ball bearing cage in the swivel bearing.

Supplied with:

Tool Rebel roller cabinet: 1 pc.

Screwdriver set 1, 18 pieces: 1 each screwdriver for slot-head No. 662200 size 4; 5.5; 6.5

1 each screwdriver for slot-head, VDE insulated, No. 663100 size 2.5; 3.5

1 each screwdriver for slot-head, Stubby size 5.5 mm

1 each screwdriver for slot-head with through blade No. 660300 size 5.5; 7

1 each screwdriver for Phillips No. 668260 size 1; 2; 3

1 each screwdriver for Phillips, Stubby No. 668260 size 2S

1 each short screwdriver for Pozidriv No. 668270 size 1; 2

1 each electronics screwdriver for Phillips size PH0
 1 each electronics screwdriver for slot-head No. 664600 size 2.5
 1 each screw gripper No. 666425 size 1; 3
 8000 A Zyklop ratchet, 1/4 inch set, 37 pieces: 1 pc. Zyklop Speed ratchet 1/4 inch No. 632390
 1 each extension 1/4 inch 75; 150mm
 1 pc. universal joint 1/4 inch
 1 pc. extension 1/4 inch "Wobble" length 56 mm
 1 each sockets for external hexagon 1/4 inch size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14; 15 mm
 1 each screwdriver bit for internal Torx®, 1/4 inch size TX8; TX9; TX10; TX15; TX20; TX25; TX27; TX30; TX40
 1 each screwdriver bit for hex socket, 1/4 inch length 28 mm size 3; 4; 5; 6; 8 mm
 1 each screwdriver bit for hex socket, 1/4 inch length 100 mm size 4; 5; 6; 8 mm
 6003 Joker set 1, 19 pieces: 1 each Joker 6003 combination spanner No. 613800 size 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24
 1 each bottle opener
 L-key set 1, 20 pieces: 1 pc. L-wrench set for hex socket with ball point, 9 pieces, metric size 1.5 – 10
 1 pc. L-wrench set for internal Torx® with ball point, 9 pieces size TX8 – TX40
 1 pc. WERA magnetiser No. 666451 size 1
 1 pc. STABILA pocket tape measure (3 metres)

Note:**Tool is supplied loose.****Technical description**

Drawer usable depth	398 mm
Number of drawers	7
Width	785 mm
Depth	518 mm
Drawer usable width	522 mm
Height	1020 mm
Manufacturer's designation	9700 Tool Rebel roller cabinet
Drawer/pull-out shelf load capacity	25 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Square drive	1/4 in
Cylinder lock	modular barrel

Type of product	Roller cabinet
-----------------	----------------

Accessories

Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 5,5 mm	660300 5,5
Blade screwdriver for slot-head, with Kraftform handle Blade width b 4 mm	662200 4
Combination spanner Width across flats 8 mm	613800 8
Combination spanner Width across flats 14 mm	613800 14
Combination spanner Width across flats 13 mm	613800 13
Screwdriver for slot-head, with Kraftform handle and impact cap Blade width b 7 mm	660300 7
Screwdriver for Phillips, with round steel blade Cross-head size 3	668260 3
Electrician's screwdriver for slot-head, with Kraftform handle fully insulated Blade width b 3,5 mm	663100 3,5
Blade screwdriver for slot-head, with Kraftform handle Blade width b 5,5 mm	662200 5,5
Combination spanner Width across flats 11 mm	613800 11
Combination spanner Width across flats 6 mm	613800 6
Screwdriver for Pozidriv, with round steel blade Cross-head size 1	668270 1
Combination spanner Width across flats 19 mm	613800 19
Electronics screwdriver for slot-head Kraftform Micro Blade width b 2,5 mm	664600 2,5
Combination spanner Width across flats 12 mm	613800 12
Combination spanner Width across flats 17 mm	613800 17
Combination spanner Width across flats 16 mm	613800 16
Screw holder Type 1	666425 1
Screwdriver for Phillips, with round steel blade Cross-head size 1	668260 1

Blade screwdriver for slot-head, with Kraftform handle Blade width b 6,5 mm	662200 6,5
Combination spanner Width across flats 18 mm	613800 18
Screw holder Type 3	666425 3
Combination spanner Width across flats 15 mm	613800 15
Combination spanner Width across flats 10 mm	613800 10
Combination spanner Width across flats 20 mm	613800 20
Screwdriver for Phillips, with round steel blade Cross-head size 2	668260 2
Electrician's screwdriver for slot-head, with Kraftform handlefully insulated Blade width b 2,5 mm	663100 2,5
Precision ratchet "Zyklop Speed" reversible, 1/4 inch with swivel head and ejector	632390
Combination spanner Width across flats 22 mm	613800 22
Combination spanner Width across flats 21 mm	613800 21
Screwdriver for Pozidriv, with round steel blade Cross-head size 2	668270 2
Combination spanner Width across flats 7 mm	613800 7
Combination spanner Width across flats 24 mm	613800 24