



## Side lock arbor, SK 40, Clamping range $\varnothing$ D1: 10mm



### Order data

Order number	302420 10
GTIN	4250122600244
Item class	36E

### Description

**Version:**

Internal thread for manual clamping.

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

### Technical description

Spare clamping screw No. 30 9900	10
Overhang dimension A	50 mm
Overall length L	143 mm
Thread M	M16
Clamping $\varnothing$ D <sub>1</sub>	10 mm
External $\varnothing$ D	35 mm
Adapter	SK 40
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

## Accessories

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
	308740 40

Special pull stud with internal thread suitable for steep tapers 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40

308802 40

Pull studsealed, form B suitable for steep tapers 40

308650 40

Spare clamping screw for chucks with clamping  $\varnothing$  D1 10 mm

309900 10