

**Short drill chuck Form A, SK 40, Clamping range: 2,5-16mm****Order data**

Order number	302540 2,5-16
GTIN	4045197307675
Item class	37D

Description**Version:**

For clockwise and anticlockwise rotation. Internal thread for manual clamping.

Application:

For clamping drills, countersinks, and reamers on milling machines.

Supplied with:

Hexagon screwdriver with T-handle.

Technical description

Overhang dimension A	97 mm
Clamping range	2.5 - 16 mm
External Ø D	56 mm
Spare chuck key	SW6
Adapter	SK 40
Arbor standard	DIN 2080
Shape	A
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studForm B suitable for steep tapers 40	308640 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studForm A suitable for steep tapers 40	308600 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Pull stud 45°sealed suitable for steep tapers 40

308760 40