

**Garant**
**Side lock arbor Form ADB with cooling channel bores, SK 50 short, Clamping range  $\varnothing$  D1: 18mm**

**Order data**

Order number	300298 18
GTIN	4045197463456
Item class	31A

**Description**
**Version:**

With Balluff/RFID chip bore.

**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping $\varnothing$ D <sub>1</sub>	18 mm
Overhang dimension A	63 mm
Spare clamping screw No. 30 9900	16
External $\varnothing$ D	50 mm
Adapter	SK 50 short
Standard	DIN 6359

Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studsealed suitable for steep tapers 50	308660 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50

Pull stud 60°sealed suitable for steep tapers 50

308785 50

Spare clamping screw for chucks with clamping  $\varnothing$  D1 16  
mm

309900 16