

HOLEX®
Side lock arbor Form AD, SK 50 A = 160, Clamping range \varnothing D1: 25 mm

Order data

Order number	300360 25
GTIN	4045197144256
Item class	32A

Description
Version:

With Balluffchip bore.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

External \varnothing D: 65 mm

Spare clamping screw 309900: 25

Technical description

Spare clamping screw 309900	25
Clamping \varnothing D ₁	25 mm
External \varnothing D	65 mm
Adapter	SK 50 A = 160
Norm	DIN 6359
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 3 \mu\text{m}$

Machining strategy

HPC

Accessories

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK

308820 50

Special pull stud with no internal thread sealed suitable for steep tapers 50

308700 50

Pull stud 45° sealed suitable for steep tapers 50

308760 50

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50

308615 50

Pull stud 90° sealed suitable for steep tapers 50

308795 50

Pull stud 60° sealed suitable for steep tapers 50

308785 50

Special pull stud with internal thread suitable for steep tapers 50

308740 50

Pull stud Form A suitable for steep tapers 50

308600 50

Special pull stud with no internal thread sealed suitable for steep tapers 50

308720 50

Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK

308830 50

Pull stud 45° sealed suitable for steep tapers 50

308765 50

Pull stud Form B suitable for steep tapers 50

308640 50

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50

308605 50

Pull stud 90° sealed suitable for steep tapers 50

308790 50

Pull stud sealed suitable for steep tapers 50

308660 50

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK

308810 50

Pull stud sealed, form B suitable for steep tapers 50

308620 50

Pull stud sealed, form A suitable for steep tapers 50

308610 50

Torque insert for Pull studs to ISO 7388 suitable for steep tapers 50 SK

308812 50

Pull stud sealed, form B suitable for steep tapers 50

308650 50