

**HOLEX®**
**MT reducing adapter with tang, Form AD, SK 50 short, MT internal: 4**

**Order data**

Order number	301200 4
GTIN	4045197145949
Item class	32A

**Description**
**Version:**

- **Ground internally and externally.**
- **With Balluffchip bore.**

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308810– 308830.

Arbor standard: DIN 69871

Arbor standard: ISO 7388-1

Shape: AD

Balance quality G at rotational speed: G 6.3 at 12,000 rpm

Concentricity:  $\leq 8 \mu\text{m}$

Overhang dimension A: 95 mm

External  $\varnothing$  D: 48 mm

**Technical description**

Overhang dimension A	95 mm
Morse taper internal	4
External $\varnothing$ D	48 mm
Adapter	SK 50 short
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1

Shape	AD
Balance quality G at rotational speed	G 6.3 at 12,000 rpm
Concentricity	≤ 8 μm

## Accessories

Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Pull stud Form B suitable for steep tapers 50	308640 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK	308830 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Pull stud sealed, form B suitable for steep tapers 50	308650 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK	308812 50
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud sealed suitable for steep tapers 50	308660 50
Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308820 50

Special pull stud with internal thread suitable for steep tapers 50

308740 50

Pull stud sealed, form A suitable for steep tapers 50

308610 50