

HOLEX®
MT reducing adapter Form A, SK 50 short, MT internal: 2

Order data

Order number	301260 2
GTIN	4045197145994
Item class	32A

Description
Version:

- **Ground internally and externally.**
- **With Balluffchip bore.**

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308810– 308830.

Arbor standard: DIN 69871

Arbor standard: ISO 7388-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 15,000 rpm

Concentricity: $\leq 8 \mu\text{m}$

Overhang dimension A: 60 mm

External \varnothing D: 32 mm

Technical description

Morse taper internal	2
Overhang dimension A	60 mm
External \varnothing D	32 mm
Adapter	SK 50 short
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1

Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 μm

Accessories

Pull stud Form B suitable for steep tapers 50	308640 50
Pull stud stud sealed, form A suitable for steep tapers 50	308610 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 50 SK	308810 50
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
Pull stud sealed, form B suitable for steep tapers 50	308650 50
Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 50 SK	308830 50
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud 45° sealed suitable for steep tapers 50	308765 50
Pull stud sealed suitable for steep tapers 50	308660 50
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
	308820 50

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 50 SK

Torque insert for Pull studs to SO 7388 suitable for steep tapers 50 SK

308812 50