

**HOLEX®**
**MT reducing adapter Form A, SK 40 short, MT internal: 2**

**Order data**

Order number	301240 2
GTIN	4045197145963
Item class	32A

**Description**
**Version:**

- **Ground internally and externally.**
- **With Balluffchip bore.**

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308810– 308830.

Arbor standard: DIN 69871

Arbor standard: ISO 7388-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 15,000 rpm

Concentricity:  $\leq 8 \mu\text{m}$

Overhang dimension A: 50 mm

External  $\varnothing$  D: 32 mm

**Technical description**

Overhang dimension A	50 mm
Morse taper internal	2
External $\varnothing$ D	32 mm
Adapter	SK 40 short
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1

Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 μm

## Accessories

Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud Form B suitable for steep tapers 40	308640 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
	308806 40

Pull stud Hurco 90° with fit sealed suitable for steep tapers 40

Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK

308810 40

Pull stud sealed suitable for steep tapers 40

308635 40

Pull stud wrench for Pull studs to DIN 69872 suitable for steep tapers 40 SK

308820 40

Pull stud Mazak sealed, form A suitable for steep tapers 40M

308670 40M

Pull stud 90° sealed suitable for steep tapers 40

308790 40

Pull stud sealed suitable for steep tapers 40

308660 40

Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40

308605 40

Pull stud 60° sealed suitable for steep tapers 40

308785 40

Pull stud sealed, form B suitable for steep tapers 40

308620 40

Pull stud wrench for Pull studs to ISO 7388 suitable for steep tapers 40 SK

308830 40