


## PRYOR

**Interchangeable numeral and letter punch set normal script 0 - 9 and A - Z,  
Character height: 5mm**



### Order data

Order number	085480 5
GTIN	5022044020160
Item class	08W

### Description

**Version:**

High precision punch holder for quick and efficient marking with **several letters and numbers at the same time.**

**Application:**

For punching into materials (e.g. identification plates, tools, machine parts etc.) with **strengths up to 1200 N/mm<sup>2</sup>.**

**Supplied with:**

100 stamp types  
12 spacers (font height 5 mm: 6 pieces)  
1 pair of tweezers  
1 hexagon L-wrench  
1 holder  
in a plastic box.

**Spare part:**

Individual type punches can be ordered under No. 085481 stating the desired font size / type (e.g. No. 085481 size 3/E).

### Technical description

Length of punch type	19.05 mm
Number of punch types that can be used	8
Height of punch type	8 mm
Character height	5 mm
Length of punch holder	39 mm
Width of punch type	4.8 mm
Type of product	Hand punch

## Accessories

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/7 mm	085481 5/7
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/E mm	085481 5/E
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/M mm	085481 5/M
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/8 mm	085481 5/8
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/V mm	085481 5/V
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/. mm	085481 5/.
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/T mm	085481 5/T
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/W mm	085481 5/W
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/U mm	085481 5/U
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/Y mm	085481 5/Y
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/L mm	085481 5/L

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/2 mm	085481 5/2
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/+ mm	085481 5/+
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/F mm	085481 5/F
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/5 mm	085481 5/5
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/R mm	085481 5/R
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/D mm	085481 5/D
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/6 mm	085481 5/6
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5LEER mm	085481 5LEER
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/H mm	085481 5/H
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/& mm	085481 5/&
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/P mm	085481 5/P
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/1 mm	085481 5/1
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/N mm	085481 5/N
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/C mm	085481 5/C
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/0 mm	085481 5/0
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/S mm	085481 5/S
Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/J mm	085481 5/J
	085481 5/G

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/G mm

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/I mm

085481 5/I

Interchangeable steel type punches Numbers range 0 – 9 Character height 5 mm

085483 5

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/Q mm

085481 5/Q

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/O mm

085481 5/O

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/, mm

085481 5/,

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/3 mm

085481 5/3

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/Z mm

085481 5/Z

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/9 mm

085481 5/9

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/A mm

085481 5/A

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/X mm

085481 5/X

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/K mm

085481 5/K

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/4 mm

085481 5/4

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5// mm

085481 5//

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/- mm

085481 5/-

Steel type punches individually exchangeable, for set No. 085480 Character height / Characters 5/B mm

085481 5/B

Steel type holder individual for set No. 085480 suitable for font 4-5 mm

085482 4-5