

MIRKA**Random orbital sander DEROS, Type: 650CV****Order data**

Order number	077324 650CV
GTIN	6416868241433
Item class	07E

Description**Version:**

The first random orbital sander with **brushless electric motor without a mains adapter.**

- **Low power consumption. Especially compact, quiet, lightweight and powerful.**
- **Low-vibration, Bluetooth interface.**
- **Can be connected to an external extraction system.**

Application:

Material removal work (coarse, intermediate, and fine abrasion) for wood, metal, and paint. Ideally suited for abrasive surfaces that are difficult to access or profiled, working wet or dry.

Note:

Suitable 6-hole abrasive disc, item No. 567775, 15-hole item No. 567558 and ABRANET item No. 567800.

Suitable backing pad item No. 567990 size 147.

Suitable hose with electric cable for external extraction system No. 077327 size 5.5.

Technical description

Weight	1 kg
maximum vibration to EN	3.4 m/s ²
Speed of oscillation	4000 - 10000 min ⁻¹
Orbital stroke	5.0 mm

Manufacturer's designation	650CV
Backing pad Ø	150 mm
Power consumption	350 W
Interface	Bluetooth interface
Power supply	Mains operated
Series	DEROS
Type of product	Orbital sander

Accessories

Velour-backed abrasive disc ABRANET® Grit 80	567800 80
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 60	567775 60
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 320	567775 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 600	567775 600
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 240	567775 240
Velour-backed abrasive disc ABRANET® Grit 240	567800 240
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 800	567775 800
Velour-backed abrasive disc ABRANET® Grit 400	567800 400
Velour-backed abrasive disc ABRANET® Grit 320	567800 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 80	567775 80
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 180	567775 180
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 120	567775 120
Velour-backed abrasive disc ABRANET® Grit 120	567800 120
Velour-backed abrasive disc ABRANET® Grit 180	567800 180
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 40	567775 40
Multi-hole PU backing pad External Ø 147 mm	567990 147
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 400	567775 400