

**MIRKA****Random orbital sander DEROS, Type: 625CV****Order data**

Order number	077324 625CV
GTIN	6416868241464
Item class	07E

**Description****Version:**

The first random orbital sander with **brushless electric motor without a mains adapter.**

- **Low power consumption. Especially compact, quiet, lightweight and powerful.**
- **Low-vibration, Bluetooth interface.**
- **Can be connected to an external extraction system.**

**Application:**

Material removal work (coarse, intermediate, and fine abrasion) for wood, metal, and paint. Ideally suited for abrasive surfaces that are difficult to access or profiled, working wet or dry.

**Note:**

Suitable 6-hole abrasive disc, item No. 567775, 15-hole item No. 567558 and ABRANET item No. 567800.

Suitable backing pad item No. 567990 size 147.

Suitable hose with electric cable for external extraction system No. 077327 size 5.5.

**Technical description**

Orbital stroke	2.5 mm
Backing pad Ø	150 mm
Weight	1 kg
Manufacturer's designation	625CV

Speed of oscillation	4000 - 10000 min <sup>-1</sup>
Power consumption	350 W
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Interface	Bluetooth interface
Power supply	Mains operated
Series	DEROS
Type of product	Orbital sander

## Accessories

Paper velour-backed abrasive disc (A)6 + 1 holes Grit 180	567775 180
Multi-hole PU backing pad External Ø 147 mm	567990 147
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 240	567775 240
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 60	567775 60
Velour-backed abrasive disc ABRANET® Grit 120	567800 120
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 320	567775 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 80	567775 80
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 40	567775 40
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 120	567775 120
Velour-backed abrasive disc ABRANET® Grit 80	567800 80
Velour-backed abrasive disc ABRANET® Grit 400	567800 400
Velour-backed abrasive disc ABRANET® Grit 320	567800 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 600	567775 600
Velour-backed abrasive disc ABRANET® Grit 240	567800 240
Velour-backed abrasive disc ABRANET® Grit 180	567800 180
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 800	567775 800
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 400	567775 400