



Linishing machine GI, Type: 790202



Order data

Order number	077613 790202
GTIN	2050001676764
Item class	03H

Description

Version:

GRIT GI linisher range for demanding industrial applications: **Sturdy design**, with **extremely power motors**.

- **High efficiency due to best removal rate.**
- **Powerful 4 kW motor (400 V, 3 ~, 50 Hz).**
- **Patented belt-tensioning system,**
- **High operational safety: Stop, linishing gap, and eye protection are individually adjustable.**

The **basic module** for industrial belt linishing.

- **Easy to use, low-vibration running.**
- **With constant speed for high metal removal rates.**
- **Can be connected to a central vacuum system.**

Application:

As a **linishing machine**, when mounted on machine mount No. 077614, with **extension modules for radial, longitudinal, surface, and centreless grinding and deburring.**

Supplied with:

CEE plug (16 A), 1 linishing belt.

Note:

For linishing belts see No. 558310 ff and No. 558453-56.

Technical description

maximum speed 2nd speed	3000 min ⁻¹
-------------------------	------------------------

Manufacturer's designation	GI 75 2H
maximum speed 1st speed	1500 min ⁻¹
Tape width	75 mm
Weight	65 kg
Band length	2000 mm
Power supply	Mains operated
Type of product	Linishing machine

Accessories

Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 120	558310 120
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60	558453 60
Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 60	558310 60
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60	558454 60
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80	558453 80
Machine mount Type 99001004	077614 99001004
Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 80	558310 80
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120	558453 120
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120	558454 120
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36	558456 36
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80	558454 80
Machine mount Type 99001003	077614 99001003

Zirconium Aluminium Oxide (ZA) finishing beltGRIT R Grit
36

558453 36

Finishing belt zirconium aluminium oxide (ZA)ZK713X Grit
40

558310 40

Zirconium Aluminium Oxide (ZA) finishing beltGRIT R Grit
36

558454 36