

# AEG

## Random orbital sander, Type: EX150ES



### Order data

Order number	077321 EX150ES
GTIN	4002395135479
Item class	07A

### Description

#### Version:

- **Powerful random orbital sander with 440 W motor.**
- **Electronic speed pre-selection. Hook and loop fastening ensures quick and simple abrasive paper replacement.**
- **2 pre-selection values for orbital stroke 3.2 mm / 6.4 mm.**
- **Integral dust extraction through 6 hole universal backing pad. Connection for external extraction system.**

#### Supplied with:

150 mm Ø backing pad for orbital sanders, additional handle, sanding disc, dust bag, extraction adapter.

#### Note:

Suitable 6-hole abrasive disc item No. 567775, 15-hole item No. 567558 and ABRANET item No. 567800.

Packaging: Carrying case

Power consumption: 440 W

Backing pad Ø: 150 mm

Orbital stroke: 3.2 / 6.4 mm

Speed of oscillation: 4000 - 10000 min<sup>-1</sup>

Weight: 2.8 kg

maximum vibration to EN: 8.5 m/s<sup>2</sup>

### Technical description

Backing pad Ø	150 mm
Orbital stroke	3.2 / 6.4 mm
maximum vibration to EN	8.5 m/s <sup>2</sup>
Manufacturer's designation	EX150ES
Weight	2.8 kg
Power consumption	440 W
Speed of oscillation	4000 - 10000 min <sup>-1</sup>
Power supply	Mains operated
Packaging	Carrying case
Type of product	Orbital sander

## Accessories

Velour-backed abrasive disc ABRANET® Grit 240	567800 240
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 600	567775 600
Velour-backed abrasive disc ABRANET® Grit 80	567800 80
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 400	567775 400
Spare base plate for EX150E / EX150ES suitable for EX150	077329 EX150
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 320	567775 320
Velour-backed abrasive disc ABRANET® Grit 320	567800 320
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 40	567775 40
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 800	567775 800
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 80	567775 80
Velour-backed abrasive disc ABRANET® Grit 400	567800 400
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 120	567775 120
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 60	567775 60
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 180	567775 180
Paper velour-backed abrasive disc (A) 6 + 1 holes Grit 240	567775 240
Velour-backed abrasive disc ABRANET® Grit 180	567800 180

Velour-backed abrasive disc ABRANET® Grit 120

567800 120