



## ER clamping nut CENTRO P for HP sealing rings, Type CP for ER: 32DI



### Order data

Order number	309665 32DI
GTIN	2050001704931
Item class	34F

### Description

#### Version:

**Mini** = all sizes with "M", extremely slim design.

**MiniSlim** = sizes with "MS", extremely super slim design.

**Conical** = all sizes with "C".

**Standard** = all other sizes.

With trapezoidal thread for high clamping forces. Extra long double guidance of the ER clamping nut. ER clamping nuts coated for reduction of **friction**.

ER clamping nut CP, **for HP sealing rings**.

#### Note:

**FAHRION system** ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

Only the nominal size can be clamped (no intermediate range!)

Clamping range: 2 - 20 mm

Overall length L: 30.1 mm

External Ø D: 50 mm

maximum tightening torque: 140 N·m

Thread: Tr40×1.5

### Technical description

Clamping range	2 - 20 mm
maximum tightening torque	140 N·m
Overall length L	30.1 mm
External Ø D	50 mm
Series	Centro P
Thread	Tr40×1.5
Type of product	Clamping nut

## Accessories

Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 6 mm	309668 6
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 15 mm	309668 15
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 5 mm	309668 5
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 12 mm	309668 12
CP roller bearing wrench for torque wrenches Type 32	309756 32
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 19 mm	309668 19
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 4 mm	309668 4
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 16 mm	309668 16
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 7 mm	309668 7
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 13 mm	309668 13
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 20 mm	309668 20

Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 18 mm	309668 18
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 9 mm	309668 9
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 11 mm	309668 11
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 8 mm	309668 8
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 2 mm	309668 2
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 3 mm	309668 3
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 10 mm	309668 10
CP roller bearing wrench Type 32	309754 32
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 17 mm	309668 17
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 14 mm	309668 14