

**Mitutoyo****Internal micrometer, Measuring range: 5-30mm****Order data**

Order number	426805 5-30
GTIN	4946368019871
Item class	44A

**Description****Version:**

Fully hardened, ground and lapped spindle. Offset and rounded jaw ends with carbide tips. Constant measuring force due to precision ratchet. Barrel with clearly engraved, black graduations. Satin chrome-plated micrometer. With adjusting screw and locking screw.

**Optional extras:**

Setting ring No. 484030.

**Technical description**

Barrel Ø	18 mm
Measuring range	5 - 30 mm
Scale divisions	0.01 mm
Error limit	5 µm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B4
Type of product	Internal micrometer

## Services

Calibration Internal micrometer maximum measuring range 50 mm

022360 50

## Accessories

Setting ring DIN 2250 C Nominal size Ø 19 mm

484030 19

Setting ring DIN 2250 C Nominal size Ø 4 mm

484030 4

Setting ring DIN 2250 C Nominal size Ø 3 mm

484030 3

Setting ring DIN 2250 C Nominal size Ø 30 mm

484030 30

Setting ring DIN 2250 C Nominal size Ø 11 mm

484030 11

Setting ring DIN 2250 C Nominal size Ø 7 mm

484030 7

Setting ring DIN 2250 C Nominal size Ø 22 mm

484030 22

Setting ring DIN 2250 C Nominal size Ø 8 mm

484030 8

Setting ring DIN 2250 C Nominal size Ø 6 mm

484030 6

Setting ring DIN 2250 C Nominal size Ø 14 mm

484030 14

Setting ring DIN 2250 C Nominal size Ø 25 mm

484030 25

Setting ring DIN 2250 C Nominal size Ø 12 mm

484030 12

Setting ring DIN 2250 C Nominal size Ø 16 mm

484030 16

Setting ring DIN 2250 C Nominal size Ø 24 mm

484030 24

Setting ring DIN 2250 C Nominal size Ø 5 mm

484030 5

Setting ring DIN 2250 C Nominal size Ø 9 mm

484030 9

Setting ring DIN 2250 C Nominal size Ø 26 mm

484030 26

Setting ring DIN 2250 C Nominal size Ø 28 mm

484030 28

Setting ring DIN 2250 C Nominal size Ø 20 mm

484030 20

Setting ring DIN 2250 C Nominal size Ø 10 mm

484030 10

Setting ring DIN 2250 C Nominal size Ø 18 mm

484030 18

Setting ring DIN 2250 C Nominal size Ø 15 mm

484030 15

Setting ring DIN 2250 C Nominal size Ø 13 mm

484030 13

Setting ring DIN 2250 C Nominal size Ø 17 mm

484030 17

