



Abrasive cloth (A) economy roll set, brown KK 114 F, 40 mm × 50 m, Number of different rolls: 10



Order data

Order number	557870 10
GTIN	2050001024602
Item class	56V

Description

Version:

Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A)**. Very good grit bonding, high abrasion performance and long service life.

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications**. This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying.

Length 50 m, pack includes integral tear-off cutter. 10 pieces = Complete set with 1 each economy roll 40 to 400 grit.

Application:

Predominantly for rubbing down metals by hand, but also suitable for all other materials.

Technical description

Number of different rolls	10
Series	KK114F
Grinding media	Standard aluminium oxide
Grinding medium code	A
Economy roll width	40 mm
Economy roll length	50 m

Product name attribute	40 mm × 50 m
Type of product	Abrasive cloth

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Abrasive cloth (A) economy roll, brownKK 114 F Grit 120	557700 120
Abrasive cloth (A) economy roll, brownKK 114 F Grit 100	557700 100
Abrasive cloth (A) economy roll, brownKK 114 F Grit 40	557700 40

Abrasive cloth (A) economy roll, brownKK 114 F Grit 150	557700 150
Abrasive cloth (A) economy roll, brownKK 114 F Grit 320	557700 320
Abrasive cloth (A) economy roll, brownKK 114 F Grit 400	557700 400
Abrasive cloth (A) economy roll, brownKK 114 F Grit 80	557700 80
Abrasive cloth (A) economy roll, brownKK 114 F Grit 60	557700 60
Abrasive cloth (A) economy roll, brownKK 114 F Grit 240	557700 240
Abrasive cloth (A) economy roll, brownKK 114 F Grit 180	557700 180