




Abrasive cloth (A) economy roll set, brown, with magazine KK 114 F, 40 mm × 50 m



Order data

Order number	557950
GTIN	2050001024657
Item class	56V

Description

Version:

Densely woven cotton cloth evenly spread with synthetic resin bonded **Aluminium Oxide (A)**. Very good grit bonding, high abrasion performance and long service life.

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications**. This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying.

The rack takes 5 economy rolls No. 557700 - 60, 80, 120, 150, 240 grit (40 mm wide, 50 m long).

Version of the advertising text:

Type **VSM KK 114 F: Brown fabric, for extremely demanding applications**. This grade is **particularly supple, resistant to oil and petroleum** and can be torn in longitudinal direction to yield clean edges without fraying. The rack takes 5 economy rolls No. 557700 - 60, 80, 120, 150, 240 grit (40 mm wide, 50 m long).

Application:

Predominantly for rubbing down metals by hand, but also suitable for all other materials.

Technical description

Series	KK114F
Grinding media	Standard aluminium oxide
Grinding medium code	A

Economy roll width	40 mm
Economy roll length	50 m
Product name attribute	40 mm × 50 m
Type of product	Abrasive cloth

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Accessories

Magazine for 5 economy rolls20 – 50 mm, 50 m	557960
----------------------------------------------	--------

Abrasive cloth (A) economy roll, brownKK 114 F Grit 120	557700 120
Abrasive cloth (A) economy roll, brownKK 114 F Grit 240	557700 240
Abrasive cloth (A) economy roll, brownKK 114 F Grit 150	557700 150
Abrasive cloth (A) economy roll, brownKK 114 F Grit 80	557700 80
Abrasive cloth (A) economy roll, brownKK 114 F Grit 60	557700 60