



## Socket set 1/4; 1/2 inch square drive 65 pieces, Type:

### Order data

Order number	630023
GTIN	4045197578105
Item class	61A

### Description

#### Version:

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

<strong>Drives / accessories</strong> to<strong> DIN 3122 / 3123</strong>;

<strong>sockets</strong> to<strong> DIN 3124</strong>. Internal / external square drives to <strong>DIN 3120</strong>.

#### Application:

For nuts / bolts gs\_profil\_6kant-einsatz M4–M20 and for hexagon socket head screws gs\_profil\_6kant M4–M18.

For cross-head screws gs\_profil\_phillips gs\_profil\_pozidriv M2–M6, slot-head screws gs\_profil\_schlitz M2.5–M5,

for internal Torx® screws gs\_profil\_torx M3–M8 and for tri-square screws gs\_profil\_vielzahn M4 – M8.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

1/4 inch hexagon sockets, SurfaceDrive: 13 pcs. No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

1/2 inch hexagon sockets, Surface Drive: 12 pcs. No. 642325 size 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34

1/2 inch hexagon screwdriver bits: 4 pcs. No. 643229 size 6; 8; 10; 14

1/4 inch hexagon bits C6.3: 4 pcs. similar to No. 675240 size 3; 4; 5; 6

1/4 inch bits for Phillips C6.3: 3 pcs. similar to No. 675310 size 1/25; 2/25; 3/25

1/4 inch Pozidriv bits C6.3: 3 pcs. similar to No. 675320 size 1/25; 2/25; 3/25

1/4 inch slot-head bits C6.3: 3 pcs. similar to No. 675250 size 3.5×0.6; 5.5×0.8; 8×1.2

1/4 inch bits for Torx® C6.3: 6 pcs. similar to No. 675340 size TX10; TX15; TX20; TX25; TX30; TX40

1/4 inch tri-square bits C6.3: 4 pcs. similar to No. 675565 size M4; M5; M6; M8

1/4 inch tommy-bar: 1 pc. No. 633029

1/4 inch spinner handle "Wobble-Fix": 1 pc. similar to No. 632829  
 1/4 inch "Wobble-Fix" extensions: 2 pcs. similar to No. 632525 size 50; 100  
 1/2 inch extensions "Wobble-Fix": 1 pc. similar to No. 641135 size 125  
 1/4 inch universal joint: 1 pc. No. 633529  
 1/2 inch universal joint: 1 pc. No. 641629  
 1/4 inch ratchet: 1 pc. No. 632025 with ejector  
 1/2 inch ratchet: 1 pc. No. 640025 with ejector  
 1/4 inch coupling shank E6.3: 1 pc. similar to No. 675020 6.3K for 1/4 inch bits C6.3  
 1/4 inch converter: 1 pc. similar to No. 650005 size 2 gs\_profil\_6kant-kupplung 1/4 inch E6.3 -  
 gs\_profil\_4kant 1/4 inch  
 1/2 inch converter: 1 pc. similar to No. 650005 size 5 gs\_profil\_6kant-kupplung 7/16 inch E11.2 -  
 gs\_profil\_4kant 1/2 inch  
 1/4 inch bit adapter: 1 pc. similar to No. 676800 gs\_profil\_4kant-einsatz 1/4 inch -  
 gs\_profil\_6kant-schluesselhilfe 1/4 inch  
 Presented in: ABS plastic box  
 Hexagon socket profile: Surface drive  
 Square with Wobble-Fix: with angle of inclination  
 Degree of fill of a drawer in units: 8×20  
 Length: 508 mm  
 Width: 292 mm  
 Height: 60 mm  
 Square drive: 1/2 inch  
 Square drive: 1/4 inch  
 Width across flats range, Surface Drive: 4-34 mm  
 Width across flats range, hexagon wrenches: 6-14 mm

## Technical description

with QuickRelease	
Packaging	ABS plastic box
Surface	
Hexagon socket profile	Surface drive
Square with Wobble-Fix	with angle of inclination
Material	
Norm	
Width	292 mm
Length	508 mm
Height	60 mm

Degree of fill of a drawer in units

8×20

Type of product